



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



JDL6 6A 600V Class J Time Delay Fuse

Edison Fuses

Catalog Number	JDL6
Manufacturer	Edison Fuses
Description	Eaton Edison Series JDL Fuse, Time-Delay Current-Limiting Fuse, Non-Indicating, 6 A, Class J, 200 Kaic, Standard, 10, 600 V
Weight per unit	0.1100 (lbs/each)
Product Category	Dual Element

Features

amperage rating	6 A
amps	6
class	Class J
dimensions	2.2500 IN X 0.8100 IN X 0.8100 IN
Fuse Type	Class J Time Delay Fuses
interrupt rating	200 kAIC
media	Yes
Voltage	600V
Voltage Rating	600 V

Descriptions

Description	6A 600V CLASS J TIME DELAY FUSE
extra long description	MOR T626-JDL6 Class J Time Delay Fu
Features	Edison's UL Class J fuse products are offered in both Dual-Element Time-Delay (JDL) and Fast-Acting (JFL) types. Both types have 200,000 amp interrupting rating at 600Vac RMS Sym amps. Their small physical size and high performance characteristics makes Class J fuses ideal for any space-limited applications. Edison's JFL fuses are best suited for the protection of non-inductive loads such as resistive heating and lighting circuits.
Long Description	Eaton Edison series JDL fuse, Time-delay current-limiting fuse, Non-indicating, 6 A, Class J, 200 kAIC, Standard, 10, 600 V
Product Type	Class J Time Delay Fuses 600V 6a
Special Features	Non-Indicating

Manufacturer Information

Brand	Eaton
GTIN	00782634803355
Manufacturers Part Number	JDL6
UPC	782634803355



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

Packaging

Carton	1
Package	10
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Datacenters - Facilities: Critical Power
standard	CSA Certified,UL Listed,RoHS Compliant,CE Marked