



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **L614 #6 1-Hole Long Barrel Compression Lug 1/4" Bolt** *Nsi Industries*

Catalog Number	L614
Manufacturer	Nsi Industries
Description	Compression Lug, #8 Awg Conductor Size, #6 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Blue Insulation Color, 1 Conductor, +90 °C Operating Temperature, 1.772 In Overall Length, 600 V, 0.02 LB/Ea
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Cable Size	# 6 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	1/4
Voltage Rating	600 V
Warranty	1 YEAR

### **Material, Color, and Finish**

Color	Blue
-------	------

### **Dimensions and Weight**

Size	L=1.77 - W=.420 - OD=.300 - ID=.200
------	-------------------------------------

### **Descriptions**

Description	#6 1-HOLE LONG BARREL COMPRESSION LUG 1/4" BOLT
extra long description	NSI L614 CU CMP Lug Long 6 AWG 1/4
Features	1 Hole Long Barrel Copper Compression Lug 6 AWG - 1/4" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .

### **Manufacturer Information**

GTIN	00662381034007
UPC	662381034007

### **Taxonomies, Classifications, and Categories**

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - One Hole



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.02

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/4 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)