



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR5262USB Dup Rec 15A TR Spec W/3.1A Usb CHRG BN

*Pass & Seymour/Legrand*

Catalog Number	TR5262USB
Manufacturer	Pass & Seymour/Legrand
Description	Combination 15A 125V Tamper-Resistant Duplex Outlet With Two Usb Chargers - Brown
Weight per unit	0.3392 (lbs/each)
Product Category	Combination Devices

### Features

amperage rating	15
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wire Size	14 -10

### Dimensions and Weight

Depth	1.392
Height	3.281
Width	1.693

### Descriptions

Description	DUP REC 15A TR SPEC W/3.1A USB CHRG BN
extra long description	P&S TR5262USB DUP REC 15A TR SPEC W
Long Description	Combination 15A 125V Tamper-Resistant Duplex Outlet with Two USB Chargers - Brown
Product Type	Dup Rec 15A TR Spec W/3.1A Usb CHRG BN
Special Features	Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007031782
Manufacturers Part Number	TR5262USB
UPC	785007031782

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Tamper-Resistant USB Duplex Receptacle



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	50
Weight Per each	0.3392

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-15R
standard	CSA Listed, cULus, FSUL, UL Listed, RoHS