



SKU: USPA-350SS-DB

UPC: 0783669941104

Features & Benefits:

Description: Watertight Underground In-Line Splice, Dual Rated, Direct Bury, Conductor Range 350-10, UL, CSA

Specs

Additional Class Attributes

Connection	Mechanical
Number of Conductors	2
Number of Poles	1
Number of Ports / Wireways	2

Dimensions

Drive Size Main	5/16
Drive Type Main	Internal Hex
Height (IN)	2.89
Height BX (IN)	3.75
Length (IN)	9.07
Weight (LB)	0.5
Weight BX (LB)	1.895
Width (IN)	1.25
Width BX (IN)	6.5

Material and Finish

Conductor Material	Aluminum
Connector Finish	Wax
Insulation	EPDM
Material	Aluminum
Wire Binding Hardware Finish	Wax
Wire Binding Hardware Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

Bolt and Screw Sizes

Number of Wire Binding Screws per Port	1
Wire Binding Torque	350

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 3
Direct Burial	Yes
Dual Rated	Yes
NEMA Code	S-569-2
UPC Code	78366994110

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 198.2
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
RUS Listed	Yes
UL Control Number	88X4
UL / CULUS Specification	UL 486D Listed
UL File Number	E125087

Environment and Temperature

Temperature Rating	90°C
Water tight	Yes

Color

Color	Black
-------	-------

Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	350 kcmil - 10 Str
Conductor Range AL Stranded (Secondary, tap, load)	NA
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	350 kcmil - 10 Str
Conductor Range CU Stranded (Secondary, tap, load)	NA
Conductor Range AL Solid (Primary, run, main, line)	NA

Voltage

Voltage Rating	600 V
----------------	-------