



BR LAMPS : BR20, BR30, BR40

DESCRIPTION

LED BR Replacement Lamps directly replace incandescent BR lamps at a fraction of the energy cost.

FEATURES

- 80% more efficient and 30x longer life than standard incandescent
- Smooth body with ANSI standard form factor
- +25,000 hour rated life for ENERGY STAR® Approved lamps*
- 50,000 hour design life**
- Acceptable for ICAT rated downlights
- Shatter resistant for reduced risk of injury and breakage

WARRANTY

- 5 year limited warranty; see eiko.com for warranty details

APPLICATIONS

- Recessed Lighting
- Accent / Display Lighting
- Retail / Residential
- Hospitality
- Track Lighting
- Healthcare
- Office
- Hotel



* Early initial qualification for ENERGY STAR allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass ENERGY STAR requirements, manufacturers may increase the lifetime of a product as dictated by ENERGY STAR guidelines. See http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs for further details.

** Design life is based on engineering testing and probability analysis



PERFORMANCE	Power Consumption	7W	8W	11W	12W	17W
	Lumens	550	650	850	1,050	1,400
	Efficacy (LPW)	79	81	77	88	82
	CRI	80+				
	Beam	120°				
	CCT	2700K, 3000K, 4000K, 5000K				
	Life (L70)	25,000 hours*				
ELECTRICAL	Power Factor	>0.7				
	Input Voltage	120V				
CONSTRUCTION	Operating Temperature	-40°F to 104°F (-40°C to 40°C)	-4°F to 104°F (-20°C to 40°C)	-40°F to 104°F (-40°C to 40°C)		
	Base	E26				
LISTINGS	Certification(s)	ENERGY STAR® Rated; cULus Classified				
	Material Usage	RoHS Compliant; no mercury or lead				
	Environment	Dry and damp location rated				

PERFORMANCE SUMMARY

BR20:

Order Code	Item #	Lumens	Watts	CCT	CRI	Beam	MOL	MOD	Life/Hours	Replaces Incan.	ES
10763	LED7WBR20/827-DIM-G9	550	7W	2700K	80+	120°	3.82"	2.5"	25,000	55W R20	★
10764	LED7WBR20/830-DIM-G9	550	7W	3000K	80+	120°	3.82"	2.5"	25,000	55W R20	★
10765	LED7WBR20/840-DIM-G9	550	7W	4000K	80+	120°	3.82"	2.5"	25,000	55W R20	★

BR30:

Order Code	Item #	Lumens	Watts	CCT	CRI	Beam	MOL	MOD	Life/Hours	Replaces Incan.	ES
11334	LED8WBR30/827-DIM-G9B	650	8W	2700K	80+	120°	5.24"	3.74"	25,000	65W BR30	★
11335	LED8WBR30/830-DIM-G9B	650	8W	3000K	80+	120°	5.24"	3.74"	25,000	65W BR30	★
11336	LED8WBR30/840-DIM-G9B	650	8W	4000K	80+	120°	5.24"	3.74"	25,000	65W BR30	★
10747	LED11WBR30/827-DIM-G9	850	11W	2700K	80+	120°	5.12"	3.74"	25,000	65W BR30	★
10748	LED11WBR30/830-DIM-G9	850	11W	3000K	80+	120°	5.12"	3.74"	25,000	65W BR30	★
10749	LED11WBR30/840-DIM-G9	850	11W	4000K	80+	120°	5.12"	3.74"	25,000	65W BR30	★
10756	LED11WBR30/850-DIM-G9	850	11W	5000K	80+	120°	5.12"	3.74"	25,000	65W BR30	★

BR40:

Order Code	Item #	Lumens	Watts	CCT	CRI	Beam	MOL	MOD	Life/Hours	Replaces Incan.	ES
10757	LED12WBR40/827-DIM-G9	1,050	12W	2700K	80+	120°	6.26"	4.72"	25,000	80W BR40	★
10758	LED12WBR40/830-DIM-G9	1,050	12W	3000K	80+	120°	6.26"	4.72"	25,000	80W BR40	★
10759	LED12WBR40/840-DIM-G9	1,050	12W	4000K	80+	120°	6.26"	4.72"	25,000	80W BR40	★
10760	LED17WBR40/827-DIM-G9	1,400	17W	2700K	80+	120°	6.26"	4.72"	25,000	100W BR40	★
10761	LED17WBR40/830-DIM-G9	1,400	17W	3000K	80+	120°	6.26"	4.72"	25,000	100W BR40	★
10762	LED17WBR40/840-DIM-G9	1,400	17W	4000K	80+	120°	6.26"	4.72"	25,000	100W BR40	★

NOTE: Use order code when ordering. ★ENERGY STAR Rated

DIMENSIONS

