

Eaton PDG23M0090TFFL

Catalog Number: PDG23M0090TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 90A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

Photo is representative



General specifications

Product Name	Catalog Number
Eaton Power Defense molded case circuit breaker	PDG23M0090TFFL
	UPC
	786679862896
Product Length/Depth	Product Height
88.9 mm	152.4 mm
Product Width	Product Weight
104.6 mm	4.75 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL 489
	CSA
	IEC 60947-2
	CCC Marked

defaultTaxonomyAttributeLabel

Amperage Rating

90 A

Voltage rating

600 Vac

Trip Type

T-M (Fxd-Fxd) TU

Circuit breaker type

PD2 Global

Circuit breaker frame type

Complete breaker

Terminals

Standard Terminals Load Only

Frame

2

Class

Class A

Interrupt rating

65 kAIC at 480 Vac

Rated operation voltage (Ue) at AC - max

600

Switch off technique

Thermomagnetic

Voltage rating - max

600 V

Interrupt rating range

70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)

65 kAIC @480V (UL)

10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)

100 kAIC @240V (UL)

35 kAIC @600V (UL/CSA)

50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC)

22 kAIC Icu @125 Vdc

30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC)

22 kAIC Icu @250 Vdc

50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC)

100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)

Number of poles

Three-pole

Resources

3D CAD drawing package

Eaton Power Defense PDG23M0090TFFL 3D drawing

Application notes

Consulting application guide - molded case circuit breakers

Brochures

Power Defense technical selling booklet

Power Defense molded case circuit breaker selection poster

Power Defense brochure

Power Defense molded case circuit breakers - Frame 2 product aid

Catalogs

Molded case circuit breakers catalog

Certification reports

EU Declaration of Conformity - Power Defense molded case circuit breakers

Power Defense Declaration concerning California's Proposition 65

PDG2 CB report

PDG4 CB report

PDG4 CCC certification

Installation instructions

Power Defense Frame 2 multi wire connector kit -

PDG2X3(2)(4)TA2256W instructions - IL012242EN H01

Power Defense Frame 2 tunnel terminal (aluminum), 50A, 3 pole instructions - IL012236EN H03

Power Defense Frame 2 tunnel terminal (aluminum), 100A, 3 pole instructions - IL012237EN H03

Power Defense Frame 2 shunt trip UVR instructions - IL012130EN

Power Defense Frame 2 box terminal (steel), 100A, 3 pole instructions - IL012234EN H03

Power Defense Frame 2 Direct Rotary Handle Assy With Interlock Version Instructions (IL012138EN).pdf

Power Defense Frame 2 handle mech direct rotary handle instructions - IL012134EN

Power Defense Frame 2 PDG2 and PDC(E)9 breaker instructions - IL012106EN

Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA Handle Attachment Instructions (IL012260EN).pdf

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA150RF instructions - IL012244EN H01

Power Defense Frame 2 multi wire connector kit -

PDG2X3(2)(4)TA2253W instructions - IL012243EN H01

Power Defense Frame 2 box terminal (aluminum), 225A, 3 pole
instructions - IL012235EN H03

Power Defense Frame 2 handle mech variable depth rotary handle
instructions - IL012136EN

Power Defense Frame 1-2-3-4 IP door barrier assembly instructions -
IL012278EN

Power Defense Frame 2 clamp terminal (steel), 20A, 3 pole instructions -
IL012246EN H03

Power Defense Frame 2 locking devices and handle block instructions -
IL012149EN

Power Defense Frame 2 tunnel terminal (aluminum), 150A, 3 pole
instructions - IL012238EN H03

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA225RF
instructions - IL012245EN H01

Power Defense Frame 2 screw terminal_end cap kit, 225A, 3 pole
instructions - IL012258EN H01

Power Defense Frame 2 motor circuit protector (HMCP) - IL012326EN

Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring
instructions – IL012316EN

Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K
instructions- IL012239EN H01

Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN

Installation videos

Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh

Power Defense Frame 2 withTMTU, Shunt Trip_UVR Animated
Instructions.rh

Power Defense Frame 2 Locking Devices and Handle Block Animated
Instructions.pdf.rh

Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated
Instructions.rh

Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle
Animated Instructions.rh

Multimedia

Power Defense Frame 3 Variable Depth Rotary Handle Mechanism
Installation How-To Video

Power Defense Frame 2 Variable Depth Rotary Handle Mechanism
Installation How-To Video

Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video

Power Defense Frame 2 Direct Rotary Handle Mechanism Installation
How-To Video

[Eaton Power Defense for superior arc flash safety](#)

[Power Defense Frame 6 Trip Unit How-To Video](#)

[Power Defense molded case circuit breakers](#)

[Power Defense Breakers](#)

[Power Defense Frame 5 Trip Unit How-To Video](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - PDG23M0090TFFL](#)

[Time/current curves](#)

[Power Defense time current curves MCP Motor Circuit Protection – PD1, PD2, PD3](#)

[Power Defense time current curve Frame 2 - PD2](#)

[White papers](#)

[Intelligent circuit protection yields space savings](#)

[Making a better machine](#)

[Molded case and low-voltage power circuit breaker health](#)

[Single and double break MCCB performance revisited](#)

[Molded case and low-voltage breaker health](#)

[Safer by design: arc energy reduction techniques](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia