

Flashlights

NEW!

LED Penlight Flashlight



- Bright, powerful 5 mm Nichia white LED light with 50,000 hours of lamp life.
- 8-lumen tested light-output produces a bright LED beam.
- 50 hours of battery life so you won't be left in the dark.
- Push-button on/off switch provides constant or momentary modes.
- The clip and body are molded from unbreakable Xenoy® as one unit, so the clip will not break off.
- Xenoy® body is resistant to chemicals, water and corrosion.
- Lightweight, slim profile design fits neatly in your shirt pocket and comfortably in your hand.

Cat. No.	Batteries Included	Overall Length	Weight (oz.)†
X3	3 AAAA Alkaline	6.2" (15.7 cm)	1.2

Xenon Pocket Flashlight



- Xenon lamp module produces a bright, powerful white beam.
- 7-lumen tested light-output generates a strong beam.
- 2 hours of battery life.
- Xenoy® body is resistant to chemicals, water and corrosion.
- Durable polycarbonate, O-ring sealed shroud.
- Twist on/off activation prevents accidental switch activation.
- Submersible to 500 feet.
- Small enough to fit in your pocket.
- Includes shirt clip and 90° "lightbender".

Cat. No.	Batteries Included	Overall Length	Weight (oz.)†
X7	2 AAA Alkaline	4.09" (10.4 cm)	1.6

LED Clip-On Flashlight



- Dual super bright, powerful 5 mm Nichia white LED lights with 10,000 hours of lamp life.
- 6-lumen tested light-output generates a strong beam.
- 100 hours of battery life so you won't be left in the dark.
- Light turns on when swivel head is flipped up.
- Head pivots to a full 180° for light where you need it.
- Body made of virtually indestructible Xylex™.
- Multiple use built-in clip attaches to surfaces up to 1/2" thick.

Cat. No.	Batteries Included	Overall Length	Weight (oz.)†
X11	2 CR2032 3V Lithium	3.5" (8.9 cm)	1.0

LED Mini-Pocket Flashlight



- Bright, powerful 5 mm Nichia white LED light with 50,000 hours of lamp life.
- 9-lumen tested light-output generates a strong concentrated beam.
- 130 hours of battery life so you won't be left in the dark.
- Push-button on/off switch provides constant or momentary modes.
- Durable polycarbonate body with O-ring sealed Xenoy® shroud.
- Includes a breakaway lanyard and pocket clip for easy attachment.
- Interchangeable clear, red and green colored lens discs for multiple applications.

Cat. No.	Batteries Included	Overall Length	Weight (oz.)†
X5	4 LR44 Alkaline	2.64" (6.7 cm)	.9

LED Pocket Flashlight



- Super bright LED lamp powered by lithium – twice as bright as a conventional flashlight.
- 41-lumen tested light-output generates a strong focused beam.
- 40 hours of battery life so you won't be left in the dark.
- Push-button on/off switch provides constant or momentary modes.
- No-slip, indestructible Xenoy® Polymer body is resistant to chemicals, water and corrosion.
- The unique faceted design and knurled grip helps prevent slippage in hazardous environments.
- Durable Xenoy®, O-ring sealed shroud.
- The black oxide coated spring clip resists corrosion and attaches the X9 to shirt pockets and belts.
- Lightweight, compact design for a perfect pocket-sized flashlight.

Cat. No.	Batteries Included	Overall Length	Weight (oz.)†
X9	2 CR123 Lithium	5.27" (13.4 cm)	3.45

Recoil™ LED Grip-It™ Flashlight



- Bright, powerful 1 watt Luxeon™ Lambertion LED utilizes Recoil LED Technology™ and provides 10,000 hours of lamp life.
- 32-lumen tested light-output produces a bright LED beam.
- Recoil LED Technology™ focuses 100% of the light forward to produce a white collimated beam that's as bright as an incandescent light.
- 32 hours of battery life so you won't be left in the dark.
- One-hand safety on/off switch operation.
- Rugged ABS body with durable polycarbonate lens, O-ring sealed shroud.
- Wrist lanyard secures and suspends flashlight in close proximity.
- Submersible to 500 feet.

Cat. No.	Batteries Included	Overall Length	Weight (oz.)†
X19	4 AA Alkaline	7" (17.8 cm)	7.3

†Weight includes batteries.

▲WARNING: It is important that users of these products read, understand, and follow all instructions, cautions, and warnings that are attached to and/or packed with the product.

