



## SNA Terminal Blocks

### T&B Catalog Number:

**UPC Number:**

011512017

**Status:**

66201995589

**Description:**

Active

Gray, feed through terminal block with 10 mm spacing, 65 Amp rated UL current with screw clamp connection that accepts 20-6 AWG UL wire range

### Features

Self-locking clamp design prevents screw loosening

Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Feed Through
Color	Gray
Mounting	DIN 1-3
Series	M 10/10
Connection Technology	Screw Clamp
UL Wire Range (AWG)	20-6
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	10
Rated CSA Wire Size (AWG)	6

### Dimension Information

L x W x H (mm)	44.5 x 10 x 55.5
Spacing (mm)	10
L x W x H (in)	1.75 x 0.394 x 2.18
Spacing (inches)	0.394

### Specifications

UL Current (Amps)	65
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	6
IEC Voltage (VAC)	800
IEC Current (Amps)	57
CSA Voltage (VAC)	600
CSA Current (Amps)	70

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500

T&B Sold in UOM	Each
T&B Weight Per UOM	0.04 lbs. Each

#### **Certifications**

Approvals	UL, IEC, CSA
-----------	--------------

#### **For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)