



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 0925 TB Medium-Duty, Tubular Clamp, Channel Mount

*Ideal*

Catalog Number	0925
Manufacturer	Ideal
Description	
Weight per unit	0.0300 (lbs/each)
Product Category	Screws, Nuts, Bolts, Washers

### Features

amperage rating	30 A
connection	Tubular Clamp, 10-32 Combo Head
Material	POLYESTER
Spacing	3/8 IN
Voltage Rating	600 A
Wire Size	10 - 22 AWG

### Material, Color, and Finish

Color	Gray 0
-------	--------

### Descriptions

Description	TB MEDIUM-DUTY, TUBULAR CLAMP, CHANNEL MOUNT
Product Type	TB 600V 30A CHNL Clamp
Special Features	This family of polyester blocks is ideal for high-temperature applications; The rugged material withstands temperatures up to 302 DEG F (150 DEG C); Three contact styles cover broad wire range - accept single wire or combinations from 22 - 8 AWG solid or stranded; Rated at 15 - 50 AMP per circuit; Flat-base models mount directly to surfaces, dovetail base models mount on standard channel; Only one end section needed per block assembly; Readily identifiable circuits - write directly on matte-surface of bloc

### Manufacturer Information

Brand	Ideal
GTIN	00783250541638
Manufacturers Part Number	0925
sub brand	Ideal
UPC	783250541638



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND METERS
Type	Medium Duty Terminal Block

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Package	600
Weight Per each	0.03

## Uses, Certifications, and Standards

Application	For High Temperature
Mounting	Channel Mount (Dovetail Base)

## 900 Series Medium Duty

This family of polyester blocks is ideal for high temperature applications. The rugged material withstands temperatures up to 302°F (150°C)

- Three contact styles cover broad wire range – accept single wire or combinations from 22 AWG to 8 AWG solid or stranded
- Rated at 15A to 50A per circuit
- Flat base models mount directly to surfaces; dovetail base models mount on stranded channel
- Only one end section needed per block assembly
- Readily identifiable circuits - write directly on matte surface of block
- Sections snap-fit with Heavy Duty, Intermediate Heavy Duty and Fuse blocks



### Specifications

**Center-to-Center Spacing:** .375 in.

**Voltage Rating:** 600 Volt max., Current: 50 Amp max.

**Ampacity:** #8 - #22 AWG

Catalog Number	921	0921	924	0924	925	0925	930	0930
<b>Mounting Style</b>	Direct Mount (Flat Base)	Channel Mount (Dovetail Base)	Direct Mount (Flat Base)	Channel Mount (Dovetail Base)	Direct Mount (Flat Base)	Channel Mount (Dovetail Base)	End Section (Direct Mount)	End Section (Channel Mount)
<b>Ampacity</b>	15A		50A		30A		—	—
<b>Contact Type</b>	Strap Screw		Tubular Screw		Tubular Clamp		—	—
<b>Screw Type</b>	6-32 Combo Head		10-32 Combo Head		10-32 Combo Head		—	—
<b>Screw Torque</b>	12 in./lbs.		8 in./lbs.		8 in./lbs.		—	—
<b>Wire Range (AWG)</b>	#14 to #22		#8 to #22		#10 to #22		—	—

<b>Housing Material</b>	Polyester (gray)
<b>Contact Material</b>	Copper Alloy, Zinc Plated
<b>Screw Material</b>	Steel, Zinc Plated
<b>Maximum Service Temperature</b>	150°C (302°F)
<b>Flammability</b>	UL94V-0 Rated



WIRE RANGE: Solid or Stranded

**Strap Screw**

1 #22 to 1 #14 AWG

**Tubular Screw**

1 #8 AWG, 1 #10 AWG, 1 to 3 #12 AWG, 1 to 4 #14 AWG, 1 to 4 #16 AWG, 1 to 5 #18 AWG, 1 to 10 #22 AWG

**Tubular Clamp**

1 #10 AWG, 1 or 2 #12 AWG, 1 to 3 #14 AWG, 1 to 4 #16 AWG, 1 to 5 #18 AWG, 1 to 10 #22 AWG