

S29936 T8 LED

12T8/LED/48-840/DR

Lamp Type	LED
Bulb Type	T8
Base Type	G13
Wattage	12
Color Temperature	4000
Color Rendering Index CRI	82



Lighting Facts Per Bulb

Brightness 1800 lumens

Estimated Energy Cost \$1.45

per year, based on 3 hrs/day, 11c/kWh.
Energy cost depends on utility rates and light use.

Average Life 45.7 years

Based on 3 hrs/day

Light Appearance



Energy Used 12 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29936	LED	*	n/a	12	n/a	T8	Medium Bi Pin
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
G13	12T8/LED/48-840/DR	n/a	n/a	48	1	1800	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	82	210	10	sleeve	n/a	Yes

S29936 T8 LED

12T8/LED/48-840/DR

Lamp Type	LED
Bulb Type	T8
Base Type	G13
Wattage	12
Color Temperature	4000
Color Rendering Index CRI	82



Lighting Facts Per Bulb

Brightness 1800 lumens

Estimated Energy Cost \$1.45

per year, based on 3 hrs/day, 11c/kWh.
Energy cost depends on utility rates and light use.

Average Life 45.7 years

Based on 3 hrs/day

Light Appearance



Energy Used 12 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29936	LED	*	n/a	12	n/a	T8	Medium Bi Pin
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
G13	12T8/LED/48-840/DR	n/a	n/a	48	1	1800	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	82	210	10	sleeve	n/a	Yes