Data Sheet

September 2013

Product Description Use a 3M[™] Wire Connector O/B+ to electrically connect two or more conductor ends in a pigtail application and insulate the connection.

Agency Approvals & Self Certifications





Canadian Standards Association Standard NO. 22.2 NO. 188-M1983

3M File NO. LR15503



IEC Publications 685-1 and 685-2-4 3M File NO. E95240

UL Listed

As a Pressure Wire Connector tested per UL Standard 486C UL File No. E23438

Operating Temperature: 105°C (221°F) Voltage Rating: 600 volts max. Building wire 1000 volts max. signs and lighting fixtures (luminaries)

Flammability Rating: UL94 V-2

CSA Certified

CSA Standard C22.2 No. 188-M1983, CSA File No. LR15503 Operating Temperature: 105°C (221°F) Voltage Rating: 600 volts max. Building wire 1000 volts max. signs and lighting fixtures (luminaries)

Flammability Rating: C22.2 No. 0.6 V-2

Federal Specification W-S-610

"Commercial Package Only"

Туре	Class	Kind	Style		
1	1	cu	G		

Applications

AWG Range: COPPER conductors only, No. 22 thru No. 12 solid and/or stranded.

METRIC Range: COPPER conductors only, 0,5 mm 2 thru 2,5 mm2, ridged (solid or stranded) and flexible (See wire matrix for specific wire combinations.)




Weight: 0.0025 lbs. (1,13 gm) **Specifications -**Product

Construction:

Spring: Spring steel, corrosion-resistant coating

Insulator: Flame retardant, polypropylene and thermoplastic elastomer, color coded; orange/blue



Typical Physical and Electrical Properties

Performance Test (The following tests were performed to the specifications of UL Standard 486C and CSA Standard C22.2 No. 188-M1983.) unless stated

Test	Typical Value		
Static -Heathing	Pass		
Secureness	Pass		
Pullout	Pass		
Dielectric Voltage Withstand	Pass		
Secureness-Of-Insulation	Pass		
Flammability	Pass		
Salt Spray (Per MIL-STS-1344A Method 1001.1)	Pass		
Vibration (Per MIL-STS-1344A Method 2005.1)	Pass		
UV Exposure (Per ASTM G-53-77)	Pass		

Fluid Immersion Test

Typical Reagents and Materials From ASTM D 543-87	and MIL-STD-1344A (Connectors were immersed in the
following chemicals for seven days at 23°C ±2°C.	
Acetic Acid	Pass
Acetone	Pass
Detergent Solution, Heavy Duty	Pass
Ethyl Alcohol (95%)	Pass
Ethyl Alcohol (50%)	Pass
Heptane	Pass
Hydrogen Peroxide Solution 28%	Pass
Methyl Alcohol	Pass
Sodium Hydroxide Solution	Pass
Mineral Sprit	Pass
Lubricating Oil	Pass

Installation Techniques

Turn power off before installing or removing connector. All electrical work should be done according to appropriate electrical codes.

- 1. Strip wire insulation: 22–16 AWG = 5/8" 14–12 AWG = 1/2"
- 2. Firmly grasp wires, making sure insulation ends are even and tightly bundled. (Wires may be twisted or untwisted.) Lead stranded wires slightly. Slip the connector over wire tips.
- 3. Turn connector onto wires in clockwise direction until secure.
- 4. To remove, turn connector counter-clockwise.

Wire Matrix

Nire I	Matrix			MetricW	/ire Combir	nation						
				Cross Section Capacity 1,0 mm ² through 5,0 mm ²				mm ²				
22 3 STR				Conduct	tor Combin	ations	Quan 2-(5	Size 0,5 m	m ²	sol	/pe ./str.
6	5 • • 6 •						2-5		0,75 n			./str.
	1						2-4		1,0 m			./str.
SOL 4	2 • • • 3 • • 4 • 5 •			*Only A	NG wire size	e combinat	2-4 3 ions are l		1,5 m 2,5 m	m²	s	./str. ol.
20 STR 2	1 2 3 4 5		•••									
20 SOL 2		•••	•••	•••								
18 2 STR 3				:	••••							
18 2 SOL 3												
16 2 STR 2												
16 SOL 2								:				
		••••	••••	••••	••••	••••	::•	:::	::		_	
14 SOL		••••	•••	••••	:	:		:::	:•	::		_
12 1 STR 2	1 2				••••	••••	•••	•••	••	••	•	
12 1 SOL 2	1				••••	:	•••	•••	••	••	•	:
	123456	123456	12345	12345	1234	1234	123	123	12	12	1	1
	- 22	22	20	20	18	18	16	16	14	14	12	12

Shelf-Life & Storage	This product has a 5-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).
Availability	Please contact your local distributor; available from 3M.com/electrical {Where to Buy} or call 1-800-245-3573.

3M is a trademark of 3M Company.

Important Notice	All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.
Warranty; Limited Remedy; Limited Liability	This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electrical Markets Division 6801 River Place Blvd. Austin, TX 78726-9000 800.245.3573 FAX: 800.245.0329 www.3M.com/electrical

Please recycle © 3M 2013 All rights reserved 78-8121-1125-6 Rev D