

Type LP Pneumatic Time Delay Limit Switch

10316H1600

UPC:782113266336

Dimensions:

- **Height:** 1.78 IN
- **Length:** 1.55 IN
- **Width:** 5.06 IN

Weight:2.125 LB

Notes:ON Delay; CW and CCW; Timing Range: 0.05 to 60 seconds; ON Delay Function: Timing begins when lever is actuated and held

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 120Vac / 0.2A at 120Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 4, 13
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 0.2A
- **Operating Temperature:** 32° to 149°F (0° to 65°C)
- **Switch Type:** Side Rotary, Pneumatic Time Delay

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H1600](#)

Certifications:

- UL Listed

Product compliance:

- Contact Manufacturer

Type LP Pneumatic Time Delay Limit Switch

10316H1600

UPC:782113266336

Dimensions:

- **Height:** 1.78 IN
- **Length:** 1.55 IN
- **Width:** 5.06 IN

Weight:2.125 LB

Notes:ON Delay; CW and CCW; Timing Range: 0.05 to 60 seconds; ON Delay Function: Timing begins when lever is actuated and held

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 120Vac / 0.2A at 120Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 4, 13
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 0.2A
- **Operating Temperature:** 32° to 149°F (0° to 65°C)
- **Switch Type:** Side Rotary, Pneumatic Time Delay

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H1600](#)

Certifications:

- UL Listed

Product compliance:

- Contact Manufacturer

