


COOPER LIGHTING - METALUX®

DIMENSIONS



NOMINAL LENGTH	A	B (T8)	C (T12)
4', 6' and 8'	5-1/4" (134mm)	4-1/4" (105mm)	4-3/8" (111mm)

DESCRIPTION

The STN Series is a functional and multi-purpose heavy duty strip family that incorporates premium performance and construction durability. The performance and application versatility of this series can be increased by incorporating symmetrical or asymmetrical reflectors. The STN Series can be installed using various mounting methods and numerous options and accessories are available. The STN Series can be the illumination solution in commercial, industrial, institutional and retail applications. An excellent choice for storage/utility areas, coves, display cases, shops, task and general area lighting.



STN SERIES

4', 6', or 8' Strip
1 or 2 Lamp

COMMERCIAL HEAVY DUTY STRIPLITE

- Equipped with energy saving ballasts/complies with federal energy efficiency standards
- Die formed channel
- Baked enamel finish
- Easy wireway access/wireway cover removed without tools
- Numerous KOs for easy installation
- Spring loaded lampholders
- Also available in tandem 8' lengths
- UL/CUL Listed. Suitable for damp locations.

ORDERING INFORMATION

SAMPLE NUMBER: STN-232-120V-EB81-U


Blank=4' Length 8T=8' Length STN=Series	Number of Lamps 1 or 2 lamps (Not Included)	Ballast Type ⁽¹⁾ Blank =Standard Magnetic Ballast LE3 =T12 Magnetic Energy Saving EB8 = T8 Electronic Instant Start. Total Harmonic Distortion < 10% No. of Ballast 1, 2 or 3 EB8 /PLUS = T8 Electronic Instant Start. High Ballast Factor >1.13. Total Harmonic Distortion < 20% No. of Ballast 1, 2 or 3 ER8 = T8 Electronic Program Rapid Start. Total Harmonic Distortion < 10% No. of Ballast 1, 2 or 3 EB2 =T12 Electronic Rapid Start. No. of Ballast 1 or 2 (For complete details on generic or to specify manufacturer's ballast see pg. 469)	Options (See Options Section)	Packaging U=Unit Pack 4B=4 Bulk
	Wattage (Length) 40=34/40W T12 (48") 32=32W T8 (48") 48=40W T12 (48") SL 48HO=60W T12 (48") HO 48HO=44W T8 (48") HO 72=55W T12 (72") SL 72HO=85W T12 (72") HO 72HO=65W T8 (72") HO 96=60/75W T12 (96") SL ⁽³⁾ 96=59W T8 (96") SL 96HO=95/110W T12 (96") HO ⁽³⁾ 96HO=86W T8 (96") HO			
	Voltage ⁽¹⁾ 120V=120 Volt 277V=277 Volt 347V=347 Volt UNV=Universal Voltage 120-277 ⁽²⁾			
	Options GL=Single Element Fuse GM=Double Element Fuse Emergency - for EM installed, see EM options table			

NOTES: ⁽¹⁾Products also available in non-US voltages and frequencies for international markets. ⁽²⁾Not available when specifying emergencies, voltage must be specific.
⁽³⁾296 and 296HO with LE3 only available in 120V.

For complete product data, reference the Fluorescent Specification binder. Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Representative for availability and ordering information.

COOPER LIGHTING - METALUX®

DIMENSIONS



NOMINAL LENGTH	A	B (T8)	C (T12)
4', 6' and 8'	5-1/4" (134mm)	4-1/4" (105mm)	4-3/8" (111mm)

DESCRIPTION

The STN Series is a functional and multi-purpose heavy duty strip family that incorporates premium performance and construction durability. The performance and application versatility of this series can be increased by incorporating symmetrical or asymmetrical reflectors. The STN Series can be installed using various mounting methods and numerous options and accessories are available. The STN Series can be the illumination solution in commercial, industrial, institutional and retail applications. An excellent choice for storage/utility areas, coves, display cases, shops, task and general area lighting.



STN SERIES

4', 6', or 8' Strip
1 or 2 Lamp

COMMERCIAL HEAVY DUTY STRIPLITE

- Equipped with energy saving ballasts/complies with federal energy efficiency standards
- Die formed channel
- Baked enamel finish
- Easy wireway access/wireway cover removed without tools
- Numerous KOs for easy installation
- Spring loaded lampholders
- Also available in tandem 8' lengths
- UL/CUL Listed. Suitable for damp locations.

ORDERING INFORMATION

SAMPLE NUMBER: STN-232-120V-EB81-U

Blank=4' Length 8T=8' Length STN=Series	Number of Lamps 1 or 2 lamps (Not Included)	Wattage (Length) 40=34/40W T12 (48") 32=32W T8 (48") 48=40W T12 (48") SL 48HO=60W T12 (48") HO 48HO=44W T8 (48") HO 72=55W T12 (72") SL 72HO=85W T12 (72") HO 72HO=65W T8 (72") HO 96=60/75W T12 (96") SL ⁽³⁾ 96=59W T8 (96") SL 96HO=95/110W T12 (96") HO ⁽³⁾ 96HO=86W T8 (96") HO	Ballast Type⁽¹⁾ Blank =Standard Magnetic Ballast LE3 =T12 Magnetic Energy Saving EB8 = T8 Electronic Instant Start. Total Harmonic Distortion < 10% No. of Ballast 1, 2 or 3 EB8 /PLUS = T8 Electronic Instant Start. High Ballast Factor >1.13. Total Harmonic Distortion < 20% No. of Ballast 1, 2 or 3 ER8 = T8 Electronic Program Rapid Start. Total Harmonic Distortion < 10% No. of Ballast 1, 2 or 3 EB2 =T12 Electronic Rapid Start. No. of Ballast 1 or 2 (For complete details on generic or to specify manufacturer's ballast see pg. 469)	Options (See Options Section)	Packaging U=Unit Pack 4B=4 Bulk
	Voltage⁽¹⁾ 120V=120 Volt 277V=277 Volt 347V=347 Volt UNV=Universal Voltage 120-277 ⁽²⁾	Options GL=Single Element Fuse GM=Double Element Fuse Emergency - for EM installed, see EM options table			

NOTES: ⁽¹⁾Products also available in non-US voltages and frequencies for international markets. ⁽²⁾Not available when specifying emergencies, voltage must be specific.
⁽³⁾296 and 296HO with LE3 only available in 120V.

For complete product data, reference the Fluorescent Specification binder. Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Representative for availability and ordering information.