



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SVX040A14A1N2 SVX9000 40HP 480V NEMA1 Alfa PNL W/Conf Coat

Eaton Corp

Catalog Number	SVX040A14A1N2
Manufacturer	Eaton Corp
Description	Eaton SVX Adjustable Frequency Drive, 40HP, Nema Type 1/IP21, 480V, FR7, Three-Phase, Emc H, Standard Software, A/N Keypad, No Brake Chopper, Varnished Boards
Weight per unit	79.0 (lbs/each)
Product Category	Ac Drives

Features

dimensions	29.5000 IN X 12.7500 IN X 13.2500 IN
keypad	Alphanumeric

Descriptions

Description	SVX9000 40HP 480V NEMA1 ALFA PNL W/CONF COAT
extra long description	ETN SVX040A1-4A1N2 SVX9000 40HP 480
Features	Demand more accurate speed control. Eaton's SVX series of variable frequency drives offer sensorless vector control technology coupled with an adaptive motor model and sophisticated ASIC circuit features. This technology allows for steady speed error, fast torque rise time, high immunity to resonance vibrations and high starting torque and current. The SVX9000 is suitable for multiple motor drive systems and high-speed applications.
Long Description	Eaton SVX adjustable frequency drive, 40HP, NEMA Type 1/IP21, 480V, FR7, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Varnished Boards
Product Type	SVX9000 40HP 480V N1 Alfa W/Conf Coat

Manufacturer Information

Brand	Eaton
GTIN	00782116103904
Manufacturers Part Number	SVX040A14A1N2
UPC	782116103904

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Adjustable frequency drive

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	79



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

EN 61800-3 Level H,UL 508C,IEC 61800-2,Contact Manufacturer