

Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



Photo is representative

General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX125A1-4A1N1
UPC	Product Length/Depth
782116011599	13.5 in
Product Height	Product Width
30.1 in	11.5 in
Product Weight	Warranty
127 lb	2 year
Compliances	Certifications
Contact Manufacturer	IEC 61800-2
	UL 508C
	EN 61800-3 Level H

Brake chopper

No brake chopper

Modification

Standard boards

Horsepower

125 hp

Frame size

8

Keypad

Alphanumeric

Input

EMC H

Three-phase

Rating

NEMA 1, IP21

Software

Standard

Application notes

SPI - Variable frequency drives with a common DC bus

Electromagnetic compatibility (EMC)

Connecting drives to generator supplies

Brochures

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

Catalogs

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - SVX125A1-4A1N1

Drawings

SVX_(FR8) 3D Inventor

SVX_(FR8) AutoCAD 2D Footprint

SVX_(FR8) 2D Drawing Xchange

SVX_(FR8) AutoCAD 2D Footprint (mm)

SVX_(FR8) 2D PDF

SVX_(FR8) 3D Model Xchange

SVX and SPX Series FR4-FR11 PDF Open Drawings

Installation instructions

9000X AFD User Manual

Specifications and datasheets

Eaton Specification Sheet - SVX125A1-4A1N1

Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



Photo is representative

General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX125A1-4A1N1
UPC	Product Length/Depth
782116011599	13.5 in
Product Height	Product Width
30.1 in	11.5 in
Product Weight	Warranty
127 lb	2 year
Compliances	Certifications
Contact Manufacturer	IEC 61800-2
	UL 508C
	EN 61800-3 Level H

Brake chopper

No brake chopper

Modification

Standard boards

Horsepower

125 hp

Frame size

8

Keypad

Alphanumeric

Input

EMC H

Three-phase

Rating

NEMA 1, IP21

Software

Standard

Application notes

SPI - Variable frequency drives with a common DC bus

Electromagnetic compatibility (EMC)

Connecting drives to generator supplies

Brochures

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

Catalogs

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - SVX125A1-4A1N1

Drawings

SVX_(FR8) 3D Inventor

SVX_(FR8) AutoCAD 2D Footprint

SVX_(FR8) 2D Drawing Xchange

SVX_(FR8) AutoCAD 2D Footprint (mm)

SVX_(FR8) 2D PDF

SVX_(FR8) 3D Model Xchange

SVX and SPX Series FR4-FR11 PDF Open Drawings

Installation instructions

9000X AFD User Manual

Specifications and datasheets

Eaton Specification Sheet - SVX125A1-4A1N1