



Nonmetallic PVC Schedule 40 Conduit

CANTEX Schedule 40 PVC Conduit is designed for underground or aboveground applications, and it is backed by over 60 years of manufacturing excellence.

- Nonmetallic PVC material which is corrosion, rust and sunlight resistant
- ETL listed
- Conforms to UL651 and NEMA TC-2
- Rated for use with 90-degree C conductors
- Made in USA
- Sunlight Resistant
- 10' Lengths
- 20' Lengths available (See note below)



Nonmetallic PVC Schedule 40 Conduit Belled End - 10' Lengths



Part No.	Size	Feet per Pack	T Min	OD	ID Min	E	B	D Nom	L Min
A52AE12	1/2	6,000	.109	.840	.578	.852	.836	1.500	120
A52AG12	3/4	4,400	.113	1.050	.780	1.064	1.046	1.750	120
A52BA12	1	3,600	.133	1.315	1.004	1.330	1.310	2.000	120
A52BC12	1-1/4	3,300	.140	1.660	1.335	1.677	1.655	2.250	120
A52BE12	1-1/2	2,250	.145	1.900	1.564	1.918	1.894	2.500	120
A52CA12	2	1,400	.154	2.375	2.021	2.393	2.369	3.000	120
A52CE12	2-1/2	930	.203	2.875	2.414	2.890	2.868	3.250	120
A52DA12	3	880	.216	3.500	3.008	3.515	3.492	3.750	120
A52DE12	3-1/2	630	.226	4.000	3.486	4.015	3.992	4.000	120
A52EA12	4	570	.237	4.500	3.961	4.515	4.491	4.500	120
A52FA12	5	380	.258	5.563	4.975	5.593	5.553	5.500	120
A52GA12	6	260	.280	6.625	5.986	6.658	6.614	6.125	120
A52JA12*	8	180	.322	8.625	7.853	8.670	8.610	6.375	120

* Not ETL Listed

Dimensions are nominal


PVC Schedule 40 Conduit Belled End-20' Lengths

CANTEX Schedule 40 Conduit is available in 20' lengths with the exception of the 1/2 inch trade size. The measurements for each trade size listed above are the same with the exception of the length (L) which is 240 inches. The following is a list of the product numbers for each 20" conduit trade size: A52AG42 is the 3/4" trade size; A52BA42 is the 1" trade size; A52BC42 is the 1 1/4 " trade size; A52BE42 is the 1 1/2' trade size; A52CA42 is the 2" trade size; A52CE42 is the 2 1/2" trade size; A52DA42 is the 3" trade size; A52DE42 is the 3 1/2" trade size; A52EA42 is the 4" trade size; A52FA42 is the 5" trade size; and A52GA42 is the 6" trade size.


Nonmetallic PVC Schedule 80 Conduit

CANTEX Schedule 80 PVC Conduit is designed for underground or aboveground applications that are at risk of physical damage.

- Nonmetallic PVC material which is corrosion, rust & sunlight resistant
- ETL listed
- Conforms to UL651 and NEMA TC-2
- Rated for use with 90-degree C conductors
- Made in USA
- Sunlight Resistant
- 10' Lengths
- 20' Lengths available (See note below)



Nonmetallic PVC Schedule 80 Conduit Belled End - 10' Lengths



Part No.	Size	Feet per Pack	T Min	OD	ID Min	E	B	D Nom	L Min
A53AE12	1/2	6,000	.147	.840	.502	.852	.836	1.500	120
A53AG12	3/4	4,400	.154	1.050	.698	1.064	1.046	1.750	120
A53BA12	1	3,600	.179	1.315	.910	1.330	1.310	2.000	120
A53BC12	1-1/4	3,300	.191	1.660	1.227	1.677	1.655	2.250	120
A53BE12	1-1/2	2,250	.200	1.900	1.446	1.918	1.894	2.500	120
A53CA12	2	1,400	.218	2.375	1.881	2.393	2.369	3.000	120
A53CE12	2-1/2	930	.276	2.875	2.250	2.890	2.868	3.250	120
A53DA12	3	880	.300	3.500	2.820	3.515	3.492	3.750	120
A53DE12	3-1/2*	630	.318	4.000	3.486	4.015	3.992	4.000	120
A53EA12	4	570	.337	4.500	3.737	4.515	4.491	4.500	120
A53FA12	5	380	.375	5.563	4.713	5.593	5.553	5.500	120
A53GA12	6	260	.432	6.625	5.646	6.658	6.614	6.125	120

Dimensions are nominal

PVC Schedule 80 Conduit Belled End-20' Lengths

CANTEX Schedule 80 Conduit is available in 20' lengths with the exception of the 1/2 and 3/4 inch trade sizes. The measurements for each trade size listed above are the same with the exception of the length (L) which is 240 inches. The following is a list of the product numbers for each 20' conduit trade size: A53BA42 is the 1" trade size; A53BC42 is the 1 1/4 " trade size; A53BE42 is the 1 1/2' trade size; A53CA42 is the 2" trade size; A53CE42 is the 2 1/2" trade size; A53DA42 is the 3" trade size; and A53EA42 is the 4" trade size.