



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **1350E6514 5' Diffuse Reflective, Ac/DC, Em Relay, Cable** *Eaton Corp*

Catalog Number	1350E6514
Manufacturer	Eaton Corp
Description	Eaton Enhanced 50 Series Photoelectric Sensor, Photoelectric, Right Angle, Sensor Distance: 5 FT., 3A Max Ac, SPDT Form C Relay, 3A At 240 Vac, 6.6 FT. ( 2M ) Cable, 12-240 VDC 24-240 Vac Input, Diffuse Reflective
Weight per unit	0.6700 (lbs/each)
Product Category	Photoelectric Sensors

### **Features**

connection	6.6 ft (2 m) cable
dimensions	1.9100 IN X 1.8100 IN X 2.1000 IN

### **Descriptions**

Description	5' DIFFUSE REFLECTIVE,AC/DC,EM RELAY,CABLE
extra long description	ETN 1350E-6514 5' DIFFUSE REFLECTIV
Features	Enhanced 50 series high-performance sensors offer flexibility, durability and high optical performance with a fully potted construction that makes these sensors ideal for use in areas subject to washdown, high shock and high vibration. Three output types, four time-delay functions, six sensing modes and four connection styles allow you to tailor the sensor to meet your exact needs
Long Description	Eaton Enhanced 50 Series Photoelectric Sensor, Photoelectric, Right Angle, Sensor distance: 5 Ft., 3A max AC, SPDT Form C Relay, 3A at 240 Vac, 6.6 Ft. ( 2m ) Cable, 12-240 Vdc 24-240 Vac input, Diffuse Reflective
Product Type	5' Diffuse Reflective, Acdc, Em Relay, CBL

### **Manufacturer Information**

Brand	Eaton
GTIN	00782116111459
Manufacturers Part Number	1350E-6514
UPC	782116111459

### **Taxonomies, Classifications, and Categories**

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Photoelectric Sensor

### **Packaging**

Carton	1
Weight Per each	0.67



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and  
OEMs - Other

Operating Temperature  
standard

-13° to 131°F (-25° to 55°C)

CSA Certified,Contact Manufacturer,CE Marked