ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1350E6514 5' Diffuse Reflective, Ac/DC, Em Relay, Cable

Eaton Corp

Catalog Number	1350E6514
Manufacturer	Eaton Corp
Description	Eaton Enhanced 50 Series Photoelectric Sensor, Photoelectric, Right Angle, Sensor Distance: 5 FT., 3A Max Ac, SPDT Form C Relay, 3A At 240 Vac, 6.6 FT. (2M) Cable, 12–240 VDC 24–240 Vac Input, Diffuse Reflective
Weight per unit	0.6700 (lbs/each)
Product Category	Photoelectric Sensors

Features

connection	6.6 ft (2 m) cable
dimensions	1.9100 IN X 1.8100 IN X 2.1000 IN

Descriptions

Description	5' DIFFUSE REFLECTIVE,AC/DC,EM RELAY,CABLE
extra long description	ETN 1350E-6514 5' DIFFUSE REFLECTIV
Features	Enhanced 50 series high-performance sensors offer flexibility, durability and high optical performance with a fully potted construction that makes these sensors ideal for use in areas subject to washdown, high shock and high vibration. Three output types, four time-delay functions, six sensing modes and four connection styles allow you to tailor the sensor to meet your exact needs
Long Description	Eaton Enhanced 50 Series Photoelectric Sensor, Photoelectric, Right Angle, Sensor distance: 5 Ft., 3A max AC, SPDT Form C Relay, 3A at 240 Vac, 6.6 Ft. (2m) Cable, 12–240 Vdc 24–240 Vac input, Diffuse Reflective
Product Type	5' Diffuse Reflective, Acdc, Em Relay, CBL

Manufacturer Information

Brand	Eaton
GTIN	00782116111459
Manufacturers Part Number	1350E-6514
UPC	782116111459

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Photoelectric Sensor

Packaging

Carton	1
Weight Per each	0.67

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other
Operating Temperature	-13° to 131°F (-25° to 55°C)
standard	CSA Certified,Contact Manufacturer,CE Marked