885 Louis Drive • Warminster PA • 18974

Wasp & Hornet Killer PLUSTM Insecticide

I. Product Description

Wasp & Hornet Killer PLUS™ is a fast-acting, high strength insecticide that knocks down and kills wasps, hornets, yellow jackets, bees, fire ants, scorpions and spiders on contact. Wasp & Hornet Killer PLUS™ contains no chlorinated solvents and is safe on most plastics. It features a high dielectric strength of 47,600 volts.

II. Applications

Recommended for any outdoor worker around electric and power utilities, telecommunications equipment and installation sites, bridge and tower maintenance, cable and wire installation sites, industrial plant grounds, warehouses, farm structures and buildings.

III. Features & Benefits

- Non-Chlorinated Formulation. Replaces chlorinated solvent-based wasp and hornet killers.
- Safe on most plactics. Will not damage plastic connectors and other insulating materials.
- Reaches Over 20 Feet. Provides a dense accurate spray to drench harmful insects and their nests.
- The only wasp & hornet killer in the industry with its own Safety Data Sheet right on the label. Provides
 instant access to current safety information should an accident or OSHA inspection occur. Helps comply with
 OSHA Hazard Communications Standard 29 CFR 1910.1200.

IV. Physical Properties without propellant

Flash Point	205°F (TCC)
Odor	Petroleum
Appearance	Clear liquid
Vapor Density	>2 (air = 1)
Vapor Pressure	<0.1 mm Hg
Sara Title III, Sect. 313 Chemicals	Yes
VOC Content (Fed)	11.06 g/L
Prop 65	No

Freezing Point	Not determined
Boiling Point	435°F (initial)
Solubility	Neg. in H ₂ 0
VOC %	1.4%
Specific Gravity	0.79
Propellant	CO ₂

V. Specifications and Approvals

• EPA Reg. No. 55809-3

REV. 6/12

VI. Performance Characteristics

ASTM D-877 (Dielectric Strength)	47,600 volts

VII. Directions

- It is preferable to apply this product in the evening after all the insects have returned to the nest.
- Aim valve opening at the nest and depress button, continuing to spray until the nest is soaked with the spray.
- This product is toxic to fish and other aquatic invertebrates.
- Do not apply directly to water.
- Do not contaminate water by cleaning of equipment or disposal of wastes.

VIII. Package Description

Part Number	Container Size
14010	20 oz Aerosol w/ Trigger

IX. Disposal

Disposal requirements vary by state and local jurisdiction. All used and unused product should be disposed of in conformance with local, state and federal regulations.

X. Special Use Warnings

Aerosol Cans

Do not puncture, incinerate or store above 120°F. Exposure to high temperatures may cause can to burst. Do not place in direct sunlight or near any heat source. Aerosol cans will conduct electricity. Keep away from all live electrical sources including battery terminals, solenoids, electrical panels and other electronic components. Failure to observe this warning may result in serious injury from flash fire and/or electrical shock.

General

Use only in well ventilated area. Ventilation may be improved by opening a window or door or providing mechanical assistance. Avoid continuous breathing of vapor and spray mist. Avoid contact with skin and eyes. If ventilation is not adequate, respiratory protection should be worn. For more information regarding short term and long term exposure, review this product's Material Safety Data Sheet.

DISCLAIMER: This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. All products should be tested for suitability on a particular application prior to actual use. CRC Industries, Inc. makes no representations or warranties of any kind concerning this data.

CRC Industries, Inc. Industrial Products Division Warminster, PA 18974
Technical Service: (800)521-3168 Customer Service: (800)272-4620 CRC On-Line: (215)442-6260