


## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100 65803-0000, MO Springfield Phone: 417-429-1665





**Category Description** 

Type

## **1455RD6513 55 Series 30' Retroreflective DK Relay Ac/DC Cable** Eaton Corp

3	
Catalog Number	1455RD6513
Manufacturer	Eaton Corp
Description	Eaton 55 Series Photoelectric Sensor, Photoelectric, Sensor Distance 30 FT., 3A Max Ac, 3A Max DC, 3A Ac/DC At 120 Vac / 3 VDC, 6.6 FT. (2M) Cable, 20–264 Vac 50/60 HZ or 15–30 VDC (NPN) Input
Weight per unit	5,875.0 (lbs/each)
Product Category	Photoelectric Sensors
eatures	
connection	Cable
imensions and Weight	
Height	3.19
Length	1.83
Width	1.64
escriptions	
- Description	55 SERIES 30' RETROREFLECTIVE DK RELAY AC/DC CABLE
extra long description	ETN 1455RD6513 PHOTO SENSOR,REFLEX,
Features	55 series photoelectric sensors are identical to the 50 series except without the interchangeable outputs or logic functions. They offer durability and high optical performance in a cost-effective, self-contained package. The 55 Series features sensors with AC and DC operation in a single unit. A relay option is available on these models that provides a 3 Amp SPDT relay output for high current switching.
Long Description	Eaton 55 Series Photoelectric Sensor, Photoelectric, Sensor distance 30 Ft., 3A max AC, 3A max DC, 3A AC/DC at 120 Vac / 3 Vdc, 6.6 Ft. (2m) Cable, 20–264 Vac 50/60 Hz or 15–30 Vdc (NPN input
Product Type	Photo Sensor, Reflex, 30', DK, Rel, Acdc, CBL
Nanufacturer Information	
Brand	Eaton
GTIN	00782114111055
Manufacturers Part Number	1455RD6513
UPC	782114111055

PROXIMITY SWITCHES AND CORDSETS

Photoelectric Sensor



## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100 65803-0000, MO Springfield Phone: 417-429-1665 Fax: 417-429-1666

Packaging	
Carton	1
Weight Per each	5875
Uses, Certifications, and Standards	
Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMs
Operating Temperature	-40° to 158°F (-40° to 70°C)
standard	UL Listed,CSA Certified,Contact Manufacturer