

GE OEM Load Center Parts Program

Q Line Circuit Breakers


Main Circuit Breaker Kits

- For use with PowerMark Gold OEM Interiors with TLM prefix.
- 60°/75° C Conductor Rating
- Quick-Make, Quick-Break
- Multipole Breakers Incorporate Internal Common Trip
- Box-Type Terminals

PowerMark Gold™ Main Circuit Breakers

- Two-pole, 120/240 Vac
- For use with 150–225 A PowerMark Gold load centers
- 22 kAIC RMS symmetrical
- Includes mounting base
- For Specialty Load Center interiors with a main circuit breaker and lugs, use catalog number THQMV__WL, with the appropriate main breaker rating inserted in the space.

Main-Breaker Rating,-A	Cat.-No.	
	Top-Feed	Bottom-Feed
100	THQMV100	THQMV100B
125	THQMV125	THQMV125B
150	THQMV150	THQMV150B
175	THQMV175	THQMV175B
200	THQMV200	THQMV200B
225	THQMV225	THQMV225B



THQMV200

PowerMark Plus™ Main Circuit Breakers

- Three-pole, 240 Vac
- For use with 125-225A PowerMark Plus Interiors
- Line LUGs only included
- Breaker Mounting Bracket indicated on Drawings

Ampere Rating	Catalog-Number		Wire Range
	10- kAIC	22- kAIC	
100	TQD32100X2	THQD32100X2	#1–300 Cu or 2/0–300 Al
125	TQD32125X2	THQD32125X2	
150	TQD32150X2	THQD32150X2	
175	TQD32175X2	THQD32175X2	
200	TQD32200X2	THQD32200X2	
225	TQD32225X2	THQD32225X2	

PowerMark Gold Main Circuit Breaker Kits

- Two-pole, 120/240 Vac or 240 Vac
- For use with 125 A PowerMark Gold load centers

Cat.-No.	
Main-Breaker-Kit	Description
TQMH000	Order appropriate THQL (10 kAIC) or THHQL (22 kAIC) breakers separately



TQMH000
with breaker

Main Breaker Retainers

For Main Lug Load Centers Using a Back-Fed Branch Breaker as a Main

Load-Center	Breaker	Cat.-No.	Std. Pkg.
TL (225 A max)	THQL	THQLRK	1
	TQDL	TQDLRK	
PowerMark Gold	THQL	THQLRK1	
		THQLRK2 ①	



THQLRK1

① For six- or eight-circuit load centers.