



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY24M 5.50" Ty-Rap (Bulk)

Abb Installation Products, Inc

Catalog Number	TY24M
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, , Length Of 139.7MM (5.5 Inches), Width Of 3.6MM (0.14 Inches), Tensile Strength Rating Of 178 Newtons (40 Pounds), Bulk Pack
Weight per unit	0.0010 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Bundle Diameter	0.08 to 1.38 in , 2 to 35 mm
Material	Nylon/Polyamide 6.6
Tensile Strength	40:178

Material, Color, and Finish

Color	Ivory
-------	-------

Dimensions and Weight

Length	5.4000000000000000
Thickness	0.0400000000000000
Width	0.1400000000000000

Descriptions

Description	5.50" TY-RAP (BULK)
extra long description	ABB TY24M CABLE TIE 30LB 5.5IN NAT
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, , Length of 139.7mm (5.5 Inches), Width of 3.6mm (0.14 Inches), Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack
Product Type	Cable Tie 30LB 5.5IN Nat Nylon
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210824475
Manufacturers Part Number	TY24M
UPC	786210824475



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Weight Per each	0.001

Uses, Certifications, and Standards

standard	UL E49405
----------	-----------