




Reinventing Safety All Around

1597, 2097, 1597NTLTR, 2097NTLTR, 1597TR, 2097TR, 1597TRWR, 2097TRWR, 1597TRA, 2097TRA, 1597IGTR, 2097IGTR, 1597SWTTR, 2097NA, 1597TRNA, 2097TRNA, 1597TRWRNA, 2097TRWRNA, 1597TRSG, 2097TRSG, 1597TRAPL, 2097TRAPL, 1597TRSGAPL, 2097TRSGAPL, 1597TRAAPL, 2097TRAAPL

The Pass & Seymour® Self-Test GFCI receptacle with SafeLock® Protection conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For Hospital Grade, refer to SF708R4.

Features & Benefits


Patented SafeLock® Protection: if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected.

Tamper-resistant automatic shutter system prevents young children from inserting common household objects. Now contains "invisi-shutters" for an invisible effect.

The indicator light flashes if the device fails the self-test, signalling that the GFCI should be replaced.

Side or internal screw-pressure-plate back wire termination with #14 - #10 AWG stranded or solid, copper or copper-clad conductors.

Captive screws make for easier installation.



Ground terminal clamp allows for fast installation.

Two back-wire holes per termination add wiring flexibility, eliminate pigtail and save box space.

Prevents line-load reversal miswire: No power to the face or downstream receptacles if wired incorrectly.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Thinner profile speeds installation by leaving more room for wires in the box.

Auto-ground clip assures a positive ground to metal box.

The most durable GFCI available. Exceeds UL943 voltage surge requirements.

Meets 2015 UL Requirements

2097TRLA

Field Uses/Vertical Markets

- Industrial
- Healthcare
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

Ordering Information

Specification Grade Self-Test GFCI Receptacles


Catalog Number	Description	Rating	Color	NEMA Config
1597TR*	Spec-Grade Tamper-Resistant 15 Amp GFCI	15A 125V	I, W, -, GRY, BK, LA, NI, DB, G	5-15R
1597*	Spec-Grade 15 Amp GFCI	15A 125V	I, W, -, GRY, BK, RED, LA	5-15R
1597TRA*	Spec grade Audible Alarm Tamper-Resistant GFCI 15 Amp	15A 125V	I, W, -, LA	5-15R
1597SWTTRR*CCD4	Combination Tamper-Resistant Switch/GFCI (No Federal Specification)	15A 125V	I, W, BK, LA, GRY	5-15R
1597NTLTR*CC4	Combination Tamper-Resistant 15 Amp Night Light/GFCI	15A 125V	I, W, BK, LA, NI, DB	5-15R
1597TRWR*	Spec-Grade Weather-Resistant 15 Amp GFCI	15A 125V	I, W, -, GRY, BK, LA	5-15R
2097TR*	Spec-Grade Tamper-Resistant 20 Amp GFCI	20A 125V	I, W, -, GRY, BK, RED, LA, NI, DB, G	5-20R
2097*	Spec-Grade 20 Amp GFCI	20A 125V	I, W, -, GRY, BK, RED, LA	5-20R
1597IGTR*	Spec-Grade Isolated Ground Tamper-Resistant GFCI	15A 125V	I, W, O	5-15R
2097IGTR*	Spec-Grade Isolated Ground Tamper-Resistant GFCI	20A 125V	I, W, GRY, O, LA	5-20R
2097NTLTR*	Combination Tamper-Resistant 20 Amp Night Light/GFCI	20A 125V	I, W, GRY, BK, LA	5-20R
2097TRWR*	Spec-Grade Weather-Resistant 20 Amp GFCI	20A 125V	I, W, -, GRY, BK, LA	5-20R
2097TRA*	Spec-Grade Audible Alarm Tamper-Resistant 20 Amp GFCI	20A 125V	I, W, -, LA	5-20R
1597TRNA*	NAFTA-Compliant Spec-Grade Tamper-Resistant GFCI	15A 125V	I, W, GRY, LA	5-15R
2097TRNA*	NAFTA-Compliant Spec-Grade Tamper-Resistant GFCI	20A 125V	I, W, GRY, LA	5-20R
2097NA*	NAFTA-Compliant Spec-Grade 20 Amp GFCI	20A 125V	I, W, GRY, LA, BL	5-20R
1597TRWRNA*	NAFTA-Compliant Tamper-Resistant Weather-Resistant GFCI	15A 125V	I, W, -, LA	5-15R
2097TRWRNA*	NAFTA-Compliant Tamper-Resistant Weather-Resistant GFCI	20A 125V	I, W, GRY, LA	5-20R
1597TRSGL	15A Tamper-Resistant Self-Test Simplex GFCI	15A 125V	I, W, GRY, LA, RED, -, BK	5-15R
2097TRSGL	20A Tamper-Resistant Self-Test Simplex GFCI	20A 125V	I, W, GRY, LA, RED, -, BK	5-20R
1597TRAPL	15A Tamper-Resistant Self-Test Sensitive Appliance GFCI	15A 125V	W	5-15R
2097TRAPL	20A Tamper-Resistant Self-Test Sensitive Appliance GFCI	20A 125V	W	5-20R
1597TRSGLAPL	15A Tamper-Resistant Self-Test Sensitive Appliance Simplex GFCI	15A 125V	W	5-15R
2097TRSGLAPL	20A Tamper-Resistant Self-Test Sensitive Appliance Simplex GFCI	20A 125V	W	5-20R
1597TRAAPL	15A Audible Alarm Tamper-Resistant Self-Test Sensitive Appliance GFCI	15A 125V	W	5-15R
2097TRAAPL	20A Audible Alarm Tamper-Resistant Self-Test Sensitive Appliance GFCI	20A 125V	W	5-20R

*Color Designation

I	Ivory	-	Brown	BK	Black	LA	Light Almond
W	White	GRY	Gray	RED	Red	NI	Nickel
AB	Antique Brass	DB	Dark Bronze	O	Orange	BL	Blue



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our website.

For latest specs visit www.legrand.us/passandseymour

Technical Information

3rd Party Compliance

cULus Listed File Number E42190, Standard UL498 Attachment Plugs and Receptacles, Standard UL943 for GFCIs, Federal Specification WC596, Hospital Grade, Standard CSA C22.2 No. 42 General Use Receptacles, CSA C22.2 No. 144 for GFCIs. Conforms to NEMA WD-1 and WD-6.

Note: Depth of 1.03" for Simplex, Audible Alarm and Appliance versions.

Performance

Electrical

Dielectric Voltage	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Maximum Working Voltage	125VAC
Voltage Range	102-132VAC

Mechanical

Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	Accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire
Product Identification	Ratings are a permanent part of device

Environmental

Operating Temperature	-35°C to +66°C
Maximum Humidity	95%
Flammability	UL94 V2


Material Specs

Face: Nylon
Body: Nylon
Contacts: .03" Brass (.8)
Mounting Straps: Galvanized Steel
Terminal Screws: Nickel-Plated Steel #8 - 32
Hex Head Grounding Screw: Steel (Green)
Flat Head Mounting Screws: Zinc-Plated Steel
Test/Reset Buttons: Nylon
Auto-Ground Clip: Brass Alloy
*Night Light Lens: Lexan®
**Tamper-Resistant Shutter: Thermoplastic

* For 1597NTLTR and 2097NTLTR Night Light versions only.
** For 1597TR and 2097TR Tamper-Resistant versions only.

Warranty

1 year



Dimensions for 15 & 20 Amp



Audible Alarm



Nightlight/GFCI



Simplex



Weather-Resistant



Tamper-Resistant

Also available

- USB Charging Devices
- PlugTail® Devices
- Surge Protective & Isolated Ground Devices
- Ground Continuity Monitoring Devices (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Night Lights




The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca



Reinventing Safety All Around

1597, 2097, 1597NTLTR, 2097NTLTR, 1597TR, 2097TR, 1597TRWR, 2097TRWR, 1597TRA, 2097TRA, 1597IGTR, 2097IGTR, 1597SWTTR, 2097NA, 1597TRNA, 2097TRNA, 1597TRWRNA, 2097TRWRNA, 1597TRSG, 2097TRSG, 1597TRAPL, 2097TRAPL, 1597TRSG LAPL, 2097TRSG LAPL, 1597TRAAPL, 2097TRAAPL

The Pass & Seymour® Self-Test GFCI receptacle with SafeLock® Protection conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For Hospital Grade, refer to SF708R4.

Features & Benefits


Patented SafeLock® Protection: if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected.

Tamper-resistant automatic shutter system prevents young children from inserting common household objects. Now contains "invisi-shutters" for an invisible effect.

The indicator light flashes if the device fails the self-test, signalling that the GFCI should be replaced.

Side or internal screw-pressure-plate back wire termination with #14 - #10 AWG stranded or solid, copper or copper-clad conductors.

Captive screws make for easier installation.



Ground terminal clamp allows for fast installation.

Two back-wire holes per termination add wiring flexibility, eliminate pigtail and save box space.

Prevents line-load reversal miswire: No power to the face or downstream receptacles if wired incorrectly.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Thinner profile speeds installation by leaving more room for wires in the box.

Auto-ground clip assures a positive ground to metal box.

The most durable GFCI available. Exceeds UL943 voltage surge requirements.

Meets 2015 UL Requirements

2097TRLA

Field Uses/Vertical Markets

- Industrial
- Healthcare
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

Ordering Information

Specification Grade Self-Test GFCI Receptacles


Catalog Number	Description	Rating	Color	NEMA Config
1597TR*	Spec-Grade Tamper-Resistant 15 Amp GFCI	15A 125V	I, W, -, GRY, BK, LA, NI, DB, G	5-15R
1597*	Spec-Grade 15 Amp GFCI	15A 125V	I, W, -, GRY, BK, RED, LA	5-15R
1597TRA*	Spec grade Audible Alarm Tamper-Resistant GFCI 15 Amp	15A 125V	I, W, -, LA	5-15R
1597SWTTRR*CCD4	Combination Tamper-Resistant Switch/GFCI (No Federal Specification)	15A 125V	I, W, BK, LA, GRY	5-15R
1597NTLTR*CC4	Combination Tamper-Resistant 15 Amp Night Light/GFCI	15A 125V	I, W, BK, LA, NI, DB	5-15R
1597TRWR*	Spec-Grade Weather-Resistant 15 Amp GFCI	15A 125V	I, W, -, GRY, BK, LA	5-15R
2097TR*	Spec-Grade Tamper-Resistant 20 Amp GFCI	20A 125V	I, W, -, GRY, BK, RED, LA, NI, DB, G	5-20R
2097*	Spec-Grade 20 Amp GFCI	20A 125V	I, W, -, GRY, BK, RED, LA	5-20R
1597IGTR*	Spec-Grade Isolated Ground Tamper-Resistant GFCI	15A 125V	I, W, O	5-15R
2097IGTR*	Spec-Grade Isolated Ground Tamper-Resistant GFCI	20A 125V	I, W, GRY, O, LA	5-20R
2097NTLTR*	Combination Tamper-Resistant 20 Amp Night Light/GFCI	20A 125V	I, W, GRY, BK, LA	5-20R
2097TRWR*	Spec-Grade Weather-Resistant 20 Amp GFCI	20A 125V	I, W, -, GRY, BK, LA	5-20R
2097TRA*	Spec-Grade Audible Alarm Tamper-Resistant 20 Amp GFCI	20A 125V	I, W, -, LA	5-20R
1597TRNA*	NAFTA-Compliant Spec-Grade Tamper-Resistant GFCI	15A 125V	I, W, GRY, LA	5-15R
2097TRNA*	NAFTA-Compliant Spec-Grade Tamper-Resistant GFCI	20A 125V	I, W, GRY, LA	5-20R
2097NA*	NAFTA-Compliant Spec-Grade 20 Amp GFCI	20A 125V	I, W, GRY, LA, BL	5-20R
1597TRWRNA*	NAFTA-Compliant Tamper-Resistant Weather-Resistant GFCI	15A 125V	I, W, -, LA	5-15R
2097TRWRNA*	NAFTA-Compliant Tamper-Resistant Weather-Resistant GFCI	20A 125V	I, W, GRY, LA	5-20R
1597TRSGL	15A Tamper-Resistant Self-Test Simplex GFCI	15A 125V	I, W, GRY, LA, RED, -, BK	5-15R
2097TRSGL	20A Tamper-Resistant Self-Test Simplex GFCI	20A 125V	I, W, GRY, LA, RED, -, BK	5-20R
1597TRAPL	15A Tamper-Resistant Self-Test Sensitive Appliance GFCI	15A 125V	W	5-15R
2097TRAPL	20A Tamper-Resistant Self-Test Sensitive Appliance GFCI	20A 125V	W	5-20R
1597TRSGLAPL	15A Tamper-Resistant Self-Test Sensitive Appliance Simplex GFCI	15A 125V	W	5-15R
2097TRSGLAPL	20A Tamper-Resistant Self-Test Sensitive Appliance Simplex GFCI	20A 125V	W	5-20R
1597TRAAPL	15A Audible Alarm Tamper-Resistant Self-Test Sensitive Appliance GFCI	15A 125V	W	5-15R
2097TRAAPL	20A Audible Alarm Tamper-Resistant Self-Test Sensitive Appliance GFCI	20A 125V	W	5-20R

*Color Designation

I	Ivory	-	Brown	BK	Black	LA	Light Almond
W	White	GRY	Gray	RED	Red	NI	Nickel
AB	Antique Brass	DB	Dark Bronze	O	Orange	BL	Blue



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our website.

For latest specs visit www.legrand.us/passandseymour

Technical Information

3rd Party Compliance

cULus Listed File Number E42190, Standard UL498 Attachment Plugs and Receptacles, Standard UL943 for GFCIs, Federal Specification WC596, Hospital Grade, Standard CSA C22.2 No. 42 General Use Receptacles, CSA C22.2 No. 144 for GFCIs. Conforms to NEMA WD-1 and WD-6.

Note: Depth of 1.03" for Simplex, Audible Alarm and Appliance versions.

Performance

Electrical

Dielectric Voltage	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Maximum Working Voltage	125VAC
Voltage Range	102-132VAC

Mechanical

Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	Accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire
Product Identification	Ratings are a permanent part of device

Environmental

Operating Temperature	-35°C to +66°C
Maximum Humidity	95%
Flammability	UL94 V2


Material Specs

Face: Nylon
Body: Nylon
Contacts: .03" Brass (.8)
Mounting Straps: Galvanized Steel
Terminal Screws: Nickel-Plated Steel #8 - 32
Hex Head Grounding Screw: Steel (Green)
Flat Head Mounting Screws: Zinc-Plated Steel
Test/Reset Buttons: Nylon
Auto-Ground Clip: Brass Alloy
*Night Light Lens: Lexan®
**Tamper-Resistant Shutter: Thermoplastic

* For 1597NTLTR and 2097NTLTR Night Light versions only.
** For 1597TR and 2097TR Tamper-Resistant versions only.

Warranty

1 year



**Dimensions for
15 & 20 Amp**



Audible Alarm



Nightlight/GFCI



Simplex



Weather-Resistant



Tamper-Resistant

Also available

- | | | | |
|--|--|-------------------------------|-------------------------------|
| ▪ USB Charging Devices | ▪ Ground Continuity Monitoring Devices (GCM) | ▪ Turnlok® Locking Devices | ▪ IEC 309 Industrial Products |
| ▪ PlugTail® Devices | ▪ Straight Blade Plugs & Connectors | ▪ Weatherproof Boxes & Covers | ▪ Flexcor® Wire Mesh Grips |
| ▪ Surge Protective & Isolated Ground Devices | | | ▪ Night Lights |



The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

