



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

TY24MX 5.5" Ty-Rap (Bulk)

Abb Installation Products, Inc

Catalog Number	TY24MX
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Black Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) Length Of 139.7MM (5.45 Inches), Width Of 3.6MM (0.14 Inches), Tensile Strength Rating Of 178 Newtons (40 Pounds), Bulk Pack
Weight per unit	0.0010 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Bundle Diameter	0.08 to 1.38 in , 2 to 35 mm
Material	Nylon/Polyamide 6.6
Tensile Strength	40:178

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	5.4000000000000000
Thickness	0.0400000000000000
Width	0.1400000000000000

Descriptions

Description	5.5" TY-RAP (BULK)
extra long description	ABB TY24MX CABLE TIE 5.5IN 40LB UV
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) Length of 139.7mm (5.45 Inches), Width of 3.6mm (0.14 Inches), Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack
Product Type	Cable Tie 5.5IN 40LB Uv Black
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210826448
Manufacturers Part Number	TY24MX
UPC	786210826448



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Package	10000
Weight Per each	0.001

Uses, Certifications, and Standards

standard	UL E49405
----------	-----------