



Catalog Number: U5168-XTL-200  
Item Description: 200A 4T RL OU MAIN 8CRT  
UPC Code: 784572475311

Brand Name: Milbank

Type: Ringless Meter Socket

Application: Meter Socket with Main and Load Center

Standard: UL Listed

Voltage Rating: Up to 240 Volts Alternating Current

Amperage Rating: 200 Continuous Ampere

Phase: 1 Phase

Frequency Rating: 60 Hertz

Number Of Cutouts: 1

Cutout Size: 200 Ampere Main Breaker

Cable Entry: Overhead and Underground



Terminal: Lay in Line Side and Single Mechanical Load Side

Mounting: Surface Mount


Enclosure: Type 3R, G90 Galvanized Steel with Powder Coat



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*



FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	6	U/L MNTG.EMBOSS
B	1	1/4, 1/2 CONC. K.O.
C	4	1/2, 3/4 CONC. K.O.
D	2	1/2, 3/4, 1 CONC. K.O.
E	3	3/4, 1, 1 1/4, 1 1/2, 2 CONC. K.O.
F	1	1, 1 1/4, 1 1/2, 2, 2 1/2 CONC. K.O.
G	1	1 1/4, 1 1/2, 2, 2 1/2, 3 CONC. K.O.



Version:

1

All dimensions are +/- 1/16".  
Drawing views are not to scale.  
Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.



Catalog Number: U5168-XTL-200  
Item Description: 200A 4T RL OU MAIN 8CRT  
UPC Code: 784572475311

Brand Name: Milbank

Type: Ringless Meter Socket

Application: Meter Socket with Main and Load Center

Standard: UL Listed

Voltage Rating: Up to 240 Volts Alternating Current

Amperage Rating: 200 Continuous Ampere

Phase: 1 Phase

Frequency Rating: 60 Hertz

Number Of Cutouts: 1

Cutout Size: 200 Ampere Main Breaker

Cable Entry: Overhead and Underground



Terminal: Lay in Line Side and Single Mechanical Load Side

Mounting: Surface Mount


Enclosure: Type 3R, G90 Galvanized Steel with Powder Coat



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*



FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	6	U/L MNTG.EMBOSS
B	1	1/4, 1/2 CONC. K.O.
C	4	1/2, 3/4 CONC. K.O.
D	2	1/2, 3/4, 1 CONC. K.O.
E	3	3/4, 1, 1 1/4, 1 1/2, 2 CONC. K.O.
F	1	1, 1 1/4, 1 1/2, 2, 2 1/2 CONC. K.O.
G	1	1 1/4, 1 1/2, 2, 2 1/2, 3 CONC. K.O.



Version:

1

All dimensions are +/- 1/16".  
Drawing views are not to scale.  
Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.