



GU24 LAMP HOLDERS



TYPICAL APPLICATIONS:

- Closets
- Garages
- Attics
- Utility Rooms
- Basements
- Storage Buildings
- Commercial, Industrial, Residential, and Agricultural Lighting
- And more...



- UL Listed.
- Includes 13-watt GU24 Bi-Pin compact fluorescent lamp (CFL) and polycarbonate lamp diffuser.
- Can be used with a standard wall switch.
- 13-Watt GU24 Bi-Pin compact fluorescent lamp:
 - Lamp Output = 900 lumens
 - Lamp Color = 2700K
 - Lamp Life (approximately 10,000 hours)
- Lamp Holder Rating: 120V-250VAC, 60Hz
- Impact resistant construction.
- 7" Conductors simplify installation.
- Suitable for indoor use only.
- Medium-Base fits 3.25 inch or 4.0 inch Outlet Box.
- Meets the requirements of the 2014 National Electrical Code: Articles 410.16(A)(2), 410.52, 410.74(A)(B), 410.122.

Catalog Number	UPC Number	Description	Order Unit	Unit Qty	Unit Pkg	Units/Case	TL Case Qty	Min Order Qty	MM Req	Ship Wt (Lbs)
16530	16530	GU24 Lamp Holder: Keyless	EA	1	BX	24	24	24	Yes	11
16535	16535	GU24 Lamp Holder: Pull Chain	EA	1	BX	24	24	24	Yes	11
15675	15675	Compact Fluorescent Lamp: 13-watt, GU24 Bi-Pin, Self Ballasted Lamp (2700K)	EA	1	BX	25	25	1	No	8

Note: Lamp Holders are sold ONLY in case quantities of 24 per Carton.

UNITS OF MEASURE KEY Order Unit: The Unit to be ordered; Unit Qty: Number of pieces in each Unit; Unit Pkg: Unit Packages contained in the case - Packaging types - BG (Bag), BRL (Barrel), BX (Box), BN (Bulk), PKG (Package), EA (Each), RL (Roll), LB (Pound), C (Hundred), M (Thousand); Units/Case: Unit packages contained in the Case; TL Case Qty: The total number of items in each Master Case; Min Order Qty: The smallest Unit that can be ordered; MM Req: Must order multiples of the Unit in the stated quantities; Ship Wt (Lbs): Total weight of the units per Carton