


## ELLIOTT ELECTRIC SUPPLY 6510 Broadway St 77554-0000, TX Galveston Phone: 409-741-0072

We Deliver...Lower Cost, Quality Products, & Personal Service





### **WACDC2SPL Accessory Dimmer, (W, La, Iv)** *Eaton Wiring Devices*

Catalog Number	WACDC2SPL
Manufacturer	Eaton Wiring Devices
Description	Eaton Wi-Fi Smart Dimmer, Flush, 120V, Back and Side Wire, White, Ivory, and Light Almond, Single-Pole, Three-Way, 32°F to 104°F (0°C to 40°C), Single-Phase, Multi-Location, PC/PBT, WFD30, Wifi
Weight per unit	0.3700 (lbs/each)
Product Category	Wiring Devices

#### **Features**

dimensions	2.3600 IN X 3.7700 IN X 7.4300 IN
Phase	Single-phase
Voltage Rating	120 V

#### **Descriptions**

Description	ACCESSORY DIMMER, (W, LA, IV)
extra long description	EWD WACD-C2-SP-L Accessory Dimmer,
Features	Wi-fi smart switches, receptacles, and dimmers from Eaton set up quickly and easily with Amazon's Alexa app—no other hubs or controllers are necessary. Plus Frustration Free Setup starts the connection automatically. Schedule lights to go on and off—and even dim—to fit your daily routine. Save energy and feel more comfortable and secure. You can even add voice-control using an Amazon Echo device.
Long Description	Eaton Wi-Fi smart dimmer, Flush, 120V, Back and side wire, White, Ivory, and Light Almond, Single-pole, Three-way, 32°F to 104°F (0°C to 40°C), Single-phase, Multi-location, PC/PBT, WFD30, WiFi
Product Type	Accessory Dimmer, (W. La, Iv)

#### **Manufacturer Information**

Brand	Eaton
GTIN	00786689366698
Manufacturers Part Number	WACD-C2-SP-L
UPC	786689366698

#### **Taxonomies, Classifications, and Categories**

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Туре	Accessory



standard

# ELLIOTT ELECTRIC SUPPLY 6510 Broadway St 77554-0000, TX Galveston Phone: 409-741-0072 Fax: 409-741-0433

Packaging	
Carton	1
Package	32
Weight Per each	0.37
Uses, Certifications, and Standards	
Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities -
	Other
Operating Temperature	32 to 104 °F (0 to 40 °C)

cULus Listed