

18200 Remote-capable Battery Backup



FEATURES

- Completely self-contained, fully automatic operation.
- Compact, low-profile design in neutral finish.
- Automatic low-voltage disconnect (LVD).
- 120 or 277 VAC operation.
- V-O flame-retardant, high impact, thermoplastic housing.
- Power-on LED indicator light and push-to-test switch.
- Energy consumption: 3.2W for red letters, 3.8W for green.
- LED lamp life of 25 + years.
- Universal mounting canopy for side or top installation.
- Larger Ni-Cad emergency battery for remote capacity.

ORDERING

Product No.	Letter Color	Housing Color	Remote	Example
18200	■ R Red	■ W White	R Remote	18200RWR
Battery backup	■ G Green	■ B Black	R Remote	18200GWR

18201 Exit/Emergency Lighting Combo · Remote-capable Battery Backup



FEATURES

- Universal mounting canopy for top installation.
- 6-volt pure lead, maintenance-free battery.
- Push-to-test switch.
- Automatic low-voltage disconnect (LVD).
- 120 or 277 VAC operation.
- V-O flame-retardant, high impact, thermoplastic housing.
- Fully adjustable glare-free lighting heads.
- Energy consumption: >4W for red letters, >5W for green.
- LED lamp life of 25 + years.
- Larger emergency battery for remote capacity.

ORDERING

Product No.	Faces	Letter Color	Housing Color	Remote	Example
18201	S Single	■ R Red	■ W White	R Remote	18201SGW
	D Double	■ G Green	■ B Black	R Remote	18201DRBR