

## Product Description

High-performance coating of 95% pure zinc that electrochemically bonds with ferrous metals to form a galvanic cell. It actively fights rust and corrosion. Use as a touch-up for damaged galvanized coatings. Dries quickly.

## Product Specifications

## Applications

On threads, exposed edges, fasteners, conduit, strapping, welds, fencing, railings, grates, electrical poles, breaker panel housings, rain spouts, signs, doors, trailers, waste containers, catwalks, and guard rails.

Unit Package Description 16 Ounce Aerosol

Brand CRC

Generic Description 1 Instant Cold Galvanized Coating

Net Fill 13 Wt Oz

UPC Code 0 78254 18412 8

Unit Dimensions-Inches 7.75H x 2.63W x 2.63D

Units Per Case 12

Case Dimensions-Inches 8.69H x 8.44W x 11.31D

Cases Per Pallet 133

Lbs. Per Case 14

I 2 of 5 Code 30078254184129

Appearance Gray Viscous Liquid

Odor Aromatic

Flashpoint - TCC Method 39°F

Specific Gravity 1.49 to 1.53

Flammability Extremely Flammable

Plastic Safe Yes

Evaporation Rate >1 (butyl acetate=1)

Dry Time - Fully Dry 8 Hours

Dry Time to Tack Free 30 Minutes

Dry Time to Touch Dry 30 Minutes

Recoat 8 Hours

Average Dry Time 10 minutes

Coverage 28 to 32 Sq Ft at 3 Mil Dry

Working Temp [Degrees F] 130°F (Continuous) / 150°F (Intermittent)

Propellant Hydrocarbon

Aerosol Flammability Level I

360 Valve No

Military Specification Number Mil-P-26915, Mil-P-46105, Mil-T-26433

DOT Proper Shipping Name Consumer Commodity

VOC % (Federal) 38

VOC g/L (Federal) 574

VOC Lbs./Gal. (Federal) 4.8

Compliant For CA Yes

VOC Category Aerosol Coating: Primer

MIR Limit 1.2

Removal (How To) Remove with aromatic solvents, Xylene. Toluene can be used, but is not recommended.

