


20 AMP 125 and 250V

Industrial Grade Straight Blade Plugs and Connectors



8315-PLC



5366-CA






8415-CAT



6017-Y




Hospital Grade — 20 AMP 125V 2-Pole, 3-Wire Grounding

DESCRIPTION	CAT. NO. PLUG	CAT. NO. CONNECTOR
	NEMA 5-20P 	NEMA 5-20R  CSA config. in Canada 
Hospital Grade, Black & White Body	8315-C	8319-C
Hospital Grade, Transparent Body	8315-CT	8319-CT
Hospital Grade, Power Indication™ Transparent	8315-PLC	8319-PLC
Hospital Grade Angle, Transparent Body	8315-CAT	

Industrial Grade — 20 AMP 125V 2-Pole, 3-Wire Grounding

Black & White Nylon Body	5366-C	5369-C
Black & White Nylon Body, Power Indication™	5366-PLC	5369-PLC
All-Black Nylon, Power Indication™	5366-PLB	5369-PLB
High-Visibility Yellow Nylon Body	5366-CY	5369-CY
Gray Nylon Body	5366-CG	5369-CG
Angle, Black & White Nylon Body	5366-CA	5369-CA
Flanged Inlet, White Nylon Body	15378-C	
Flanged Outlet, White Nylon Body		15379-C

Hospital Grade — 20 AMP 250V 2-Pole, 3-Wire Grounding

DESCRIPTION	CAT. NO. PLUG	CAT. NO. CONNECTOR
	NEMA 6-20P 	NEMA 6-20R  CSA config. in Canada 
Hospital Grade Angle, Transparent Body	8415-CAT	

Industrial Grade — 20 AMP 250V 2-Pole, 3-Wire Grounding

Black & White Nylon Body	5466-C	5469-C
High-Visibility Yellow Nylon Body	5466-CY	5469-CY
Flanged Inlet, White Nylon Body	5478-C	
Flanged Outlet, White Nylon Body		5479-C

Weather-Resistant Boots

Our outstanding Industrial Grade boots feature a triple-seal design to protect straight blade and locking plugs and connectors against the harmful effects of dirt and moisture in harsh environments. Boots are available in black or high-visibility yellow. The fluted surface and grip-ring design provide a non-slip grip even in wet conditions.

DESCRIPTION	CAT. NO.
Weather-Resistant Straight Blade Plug Boot, Black Rubber. For 15A & 20A Straight Blade Industrial Nylon Plugs	6017
Weather-Resistant Straight Blade Plug Boot, High Visibility Yellow Rubber. For 15A & 20A Straight Blade Industrial Nylon Plugs	6017-Y
Weather-Resistant Straight Blade Connector Boot, Black Rubber. For 15A & 20A Straight Blade Industrial Nylon Connectors	6018
Weather-Resistant Straight Blade Connector Boot, High Visibility Yellow Rubber. For 15A & 20A Straight Blade Industrial Nylon Connectors	6018-Y

SPECIFICATIONS AND FEATURES

Hospital Grade

- Unmatched quality and performance confirmed by rigorous UL 498 testing
- Clearly identified by green dot

Industrial Grade

- Rugged construction resists impact, sunlight, chemicals and rough use
- All connector contacts are solid one-piece brass for superior conductivity
- Triple-wipe, heavy-duty power contacts set in deep pockets to resist damage
- Captive, color-coded brass #8 terminal screws
- Unique cord clamp accepts wide range of cord sizes (.245"–.700"), providing secure grip without damaging cord jacket: SVT 18-3 to SO 14-3 with strain relief insert, up to ST 10-3 when strain relief insert is removed.

- Power Indication™ devices equipped with green neon bulb rated at 30,000 hours (24/7) for 3.5 years

TESTING AND CODE COMPLIANCE

- Meet NEMA WD 1 & 6, ANSI requirements
- UL Listed & meets Fed. Spec. requirements: Industrial Plugs & Connectors (File #13393); Hospital Grade (UL 498, File #E-13393)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- Backed by a Limited 10-Year Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated V2
Operating Temperature: -40°C to 65°C