



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2095HGRED 20A 125V FD HG Gfci Deco Rec

Pass & Seymour/Legrand

Catalog Number	2095HGRED
Manufacturer	Pass & Seymour/Legrand
Description	Gfci Receptacle, Duplex; 5-20R Configuration; 2 Pole; 3 Wire; 125 Vac Voltage Rating; 20 Ampere Current Rating; High Impact Resistant Thermoplastic Material; Red Color; Back, Side Wiring; Hospital Grade
Weight per unit	0.3900 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

Current Rating	20 AMPERE
Grade	HOSPITAL
Material	HIGH IMPACT RESISTANT THERMOPLASTIC
Number of Wires	3 in
Poles	2 in
Voltage Rating	125 VAC AT 60 HZ
Wiring	BACK, SIDE

Material, Color, and Finish

Color	RED
-------	-----

Descriptions

Additional Information	Overall Dimension 1.72 Inch W x 1.13 Inch D x 4.2 Inch H; Operating Temperature -35 to 66 Deg C
Commodity Description	RECEPTACLES & SURGE PROTECTORS
Description	20A 125V FD HG GFCI DECO REC
Long Description	GFCI RECEPTACLE, DUPLEX; 5-20R CONFIGURATION; 2 POLE; 3 WIRE; 125 VAC VOLTAGE RATING; 20 AMPERE CURRENT RATING; HIGH IMPACT RESISTANT THERMOPLASTIC MATERIAL; RED COLOR; BACK, SIDE WIRING; HOSPITAL GRADE
Product Type	Gfci Receptacle

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007423570
Manufacturers Part Number	2095-HGRED
UPC	785007423570

Taxonomies, Classifications, and Categories

Category Description	Commercial GFCI devices
Type	DUPLEX

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.39

Uses, Certifications, and Standards


Approval	UL 943 (CANADA AND US), UL 498 (CANADA AND US)
Configuration	5-20R




Pass & Seymour

Straight Blade Receptacles Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1595HGW



2095HGW

Features

- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132VAC
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity
- Trip Threshold: 5± 1mA

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
Hospital Grade 15 Amp Duplex GFCI						
1595HGI	15 125	Ivory	5-15R	•	•	•
1595HGW	15 125	White	5-15R	•	•	•
1595HG	15 125	Brown	5-15R	•	•	•
1595HGGRY	15 125	Gray	5-15R	•	•	•
1595HGRED	15 125	Red	5-15R	•	•	•
1595HGLA	15 125	Light Almond	5-15R	•	•	•
Hospital Grade 20 Amp Duplex GFCI						
2095HGI	20 125	Ivory	5-20R	•	•	•
2095HGW	20 125	White	5-20R	•	•	•
2095HG	20 125	Brown	5-20R	•	•	•
2095HGGRY	20 125	Gray	5-20R	•	•	•
2095HGRED	20 125	Red	5-20R	•	•	•
2095HGLA	20 125	Light Almond	5-20R	•	•	•



NEMA
5-15R




NEMA
5-20R

Devices & Wall Plates Color Selection Chart




Pass & Seymour

Devices & Plastic Wall Plate Colors




Ivory Light Almond White Green



Black Blue Brown Gray Orange Red


See specific device and wall plate catalog charts for particular color availabilities.

Metal Wall Plates



Metal Finish Aluminum Brass (Brushed) Polished Brass Stainless Steel Brushed Bronze Chrome

Custom Metal Wall Plates Paint Finish Colors



Paint Color Orange Green Gray Yellow Glossy Black Brown White



Paint Color Primer Red Pink Flat Black Ivory Light Almond Blue

To order custom metal wall plates, see Pages Q-43 – Q-45.


For additional colors consult factory.



Pass & Seymour

Technical Specifications Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



Dimensions for
15 & 20 Amp

Typical Specifications

Manufacturer's Identification: Legrand/Pass & Seymour 1595HG
 Description: Straight Blade Duplex Hospital Grade GFCI Receptacle
 Type: 2 Pole, 3 Wire Grounding
 Rating: 20A, 125VAC Feed Thru; 15 or 20A, 125VAC Face
 3rd Party Compliance: cULus Listed, File Number E42190, Standard UL498, Attachment Plugs and Receptacles UL943 GFCIs. Federal Specification WC596 Hospital Grade. Standard CSA-C22.2 No. 42, General Use Receptacles, CSA-C22.2 No. 144 GFCIs. Conforms to NEMA WD-1 and WD-6.

Catalog Number	Color	Rating	NEMA Configuration No.
<input type="checkbox"/> 1595HGI	Ivory	15A 125VAC	5-15R
<input type="checkbox"/> 1595HGW	White	15A 125VAC	5-15R
<input type="checkbox"/> 1595HG	Brown	15A 125VAC	5-15R
<input type="checkbox"/> 1595HGGRY	Gray	15A 125VAC	5-15R
<input type="checkbox"/> 1595HGRED	Red	15A 125VAC	5-15R
<input type="checkbox"/> 1595HGCLA	Light Almond	15A 125VAC	5-15R
<input type="checkbox"/> 2095HGI	Ivory	20A 125VAC	5-20R
<input type="checkbox"/> 2095HGW	White	20A 125VAC	5-20R
<input type="checkbox"/> 2095HG	Brown	20A 125VAC	5-20R
<input type="checkbox"/> 2095HGGRY	Gray	20A 125VAC	5-20R
<input type="checkbox"/> 2095HGRED	Red	20A 125VAC	5-20R
<input type="checkbox"/> 2095HGCLA	Light Almond	20A 125VAC	5-20R

Performance

Electrical

Dielectric	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Voltage	125VAC
Voltage Range	102-132VAC

Mechanical


Indicator Light (LED)	Red, ON when GFCI is tripped
Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	#14 – #10 AWG solid or stranded copper conductor only
Product Identification	Ratings are a permanent part of the device

Environmental

Operating Temperature	-35°C to +66°C
Maximum Humidity	95%
Flammability	UL94 V2

Materials

Face	Nylon	Terminal Screws	Steel #8 - 32
Body	Nylon	Hex Head Grounding Screw	Steel (Green)
Contacts	.03" Brass (.8)	Flat Head Mounting Screw	Zinc-Plated Steel
Mounting Strap	.05" Zinc-Plated Steel (1.3)	Test/Reset Buttons	Nylon



Project

Location/Type