





Pass & Seymour

## Straight Blade Receptacles Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1595HGW



2095HGW

### Features

- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132VAC
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity
- Trip Threshold: 5± 1mA

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>Hospital Grade 15 Amp Duplex GFCI</b>						
1595HGI	15 125	Ivory	5-15R	•	•	•
1595HGW	15 125	White	5-15R	•	•	•
1595HG	15 125	Brown	5-15R	•	•	•
1595HGGRY	15 125	Gray	5-15R	•	•	•
1595HGRED	15 125	Red	5-15R	•	•	•
1595HGLA	15 125	Light Almond	5-15R	•	•	•
<b>Hospital Grade 20 Amp Duplex GFCI</b>						
2095HGI	20 125	Ivory	5-20R	•	•	•
2095HGW	20 125	White	5-20R	•	•	•
2095HG	20 125	Brown	5-20R	•	•	•
2095HGGRY	20 125	Gray	5-20R	•	•	•
2095HGRED	20 125	Red	5-20R	•	•	•
2095HGLA	20 125	Light Almond	5-20R	•	•	•



NEMA  
5-15R




NEMA  
5-20R

# Devices & Wall Plates Color Selection Chart




Pass & Seymour

## Devices & Plastic Wall Plate Colors




Ivory      Light Almond      White      Green



Black      Blue      Brown      Gray      Orange      Red


See specific device and wall plate catalog charts for particular color availabilities.

## Metal Wall Plates




**Metal Finish**      Aluminum      Brass (Brushed)      Polished Brass      Stainless Steel      Brushed Bronze      Chrome

## Custom Metal Wall Plates Paint Finish Colors



**Paint Color**      Orange      Green      Gray      Yellow      Glossy Black      Brown      White



**Paint Color**      Primer      Red      Pink      Flat Black      Ivory      Light Almond      Blue

To order custom metal wall plates, see Pages Q-43 – Q-45.


For additional colors consult factory.



Pass & Seymour

# Technical Specifications Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



Dimensions for  
15 & 20 Amp

### Typical Specifications

Manufacturer's Identification: Legrand/Pass & Seymour 1595HG  
 Description: Straight Blade Duplex Hospital Grade GFCI Receptacle  
 Type: 2 Pole, 3 Wire Grounding  
 Rating: 20A, 125VAC Feed Thru; 15 or 20A, 125VAC Face  
 3rd Party Compliance: cULus Listed, File Number E42190, Standard UL498, Attachment Plugs and Receptacles UL943 GFCIs. Federal Specification WC596 Hospital Grade. Standard CSA-C22.2 No. 42, General Use Receptacles, CSA-C22.2 No. 144 GFCIs. Conforms to NEMA WD-1 and WD-6.

Catalog Number	Color	Rating	NEMA Configuration No.
<input type="checkbox"/> 1595HGI	Ivory	15A 125VAC	5-15R
<input type="checkbox"/> 1595HGW	White	15A 125VAC	5-15R
<input type="checkbox"/> 1595HG	Brown	15A 125VAC	5-15R
<input type="checkbox"/> 1595HGGRY	Gray	15A 125VAC	5-15R
<input type="checkbox"/> 1595HGRED	Red	15A 125VAC	5-15R
<input type="checkbox"/> 1595HGCLA	Light Almond	15A 125VAC	5-15R
<input type="checkbox"/> 2095HGI	Ivory	20A 125VAC	5-20R
<input type="checkbox"/> 2095HGW	White	20A 125VAC	5-20R
<input type="checkbox"/> 2095HG	Brown	20A 125VAC	5-20R
<input type="checkbox"/> 2095HGGRY	Gray	20A 125VAC	5-20R
<input type="checkbox"/> 2095HGRED	Red	20A 125VAC	5-20R
<input type="checkbox"/> 2095HGCLA	Light Almond	20A 125VAC	5-20R

### Performance

#### Electrical

Dielectric	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Voltage	125VAC
Voltage Range	102-132VAC

#### Mechanical


Indicator Light (LED)	Red, ON when GFCI is tripped
Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	#14 – #10 AWG solid or stranded copper conductor only
Product Identification	Ratings are a permanent part of the device

#### Environmental

Operating Temperature	-35°C to +66°C
Maximum Humidity	95%
Flammability	UL94 V2

### Materials

Face	Nylon	Terminal Screws	Steel #8 - 32
Body	Nylon	Hex Head Grounding Screw	Steel (Green)
Contacts	.03" Brass (.8)	Flat Head Mounting Screw	Zinc-Plated Steel
Mounting Strap	.05" Zinc-Plated Steel (1.3)	Test/Reset Buttons	Nylon



Project
Location/Type