



PLASTIC/RUBBER SIZES

<p>SIZES SHOWN ARE FOR REFERENCE 3D MODEL IS TO BE USED FOR MANUFACTURING / VERIFICATION</p>			
<p>ALL CHANGES MUST BE APPROVED AND RECORDED BY ENGINEERING</p>			
<p>UNIT: INCHES UNLESS DUAL DIMENSION: INCH [METRIC]</p>	<p>PROJECTION  </p>	<p><b>Kraloy, a Division of Multi Fittings Corp.</b> under license</p>	
<p>THIS DRAWING AND ALL TECHNICAL INFORMATION APPEARING HEREON ARE PROPERTY OF MULTI FITTINGS CORP. AND MUST BE KEPT IN CONFIDENCE BY THE RECIPIENT. THE SAME MAY NOT BE USED OR REPRODUCED EITHER IN WHOLE OR IN PART WITHOUT THE EXPRESS CONSENT OF MULTI FITTINGS CORP.</p>	<p>TITLE 40STD6090 6"x90D PVC STD ELBOW SPxSP SCH40 KRALOY</p>		
PAPER SIZE ANSI B	NAME	DATE	SCALE: NA
PART APPEARANCE:	COLOR:	DRAWN	09/09/2020
SURFACE FINISHES: (UNLESS OTHERWISE NOTED)		APP'D	MAT'L:
INSIDE:	OUTSIDE:	OTHER:	PRODUCT CODE: 078551
DIMENSIONS ARE IN INCHES TOLERANCES (UNLESS OTHERWISE SPECIFIED) FRACTIONAL ± 1/32 X.X ± 0.015 X.XX ± 0.010 X.XXX ± 0.005 ANGULAR ± 1.0		CRITICAL DIMENSIONS ARE SHOWN AS **DIM** REFERENCE DIMENSIONS ARE SHOWN WITH REF. NOTE	
FILENAME:	FOLDER:		