


Bolt and Nut Type - Steel

Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 6-7/8

Dimension B in Inches: 1-1/4

Dimension C in Inches: 3

Application

To secure EMT or rigid conduit to threaded rod, insulator supports, or directly to mounting surface. Available with or without bolt.

Product Information

Material: Steel

Finish: Zinc electro-plate

Certifications & Codes:

CSA File Number: LR39354

UL File Number: E161206

UNSPSC: 39121701

Catalog ID: 2190

UPC Number: 781747021908

Description: Hanger, Conduit, Steel, Bolt and Nut, Trade Size 9


Application: To secure EMT or rigid conduit to threaded rod, insulator supports, or directly to mounting surface. Available with or without bolt.

Trade Size: 9

Std Pkg Qty: 10

Bolt and Nut Type - Steel

Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 6-7/8

Dimension B in Inches: 1-1/4

Dimension C in Inches: 3

Application

To secure EMT or rigid conduit to threaded rod, insulator supports, or directly to mounting surface. Available with or without bolt.

Product Information

Material: Steel

Finish: Zinc electro-plate

Certifications & Codes:

CSA File Number: LR39354

UL File Number: E161206

UNSPSC: 39121701

Catalog ID: 2190

UPC Number: 781747021908

Description: Hanger, Conduit, Steel, Bolt and Nut, Trade Size 9

Application: To secure EMT or rigid conduit to threaded rod, insulator supports, or directly to mounting surface. Available with or without bolt.

Trade Size: 9

Std Pkg Qty: 10