



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



09724 4' 16/3 Angle Cord Gry

Coleman Cable

Catalog Number	09724
Manufacturer	Coleman Cable
Description	Portable Cord Set, Stranded, 26/30 MM Core Strands, #16 Awg Conductor Size, Copper Conductor Material, PVC Insulation Material, 13 A, Gray, 3 Conductors, 4 FT Overall Length, 0.059 In Outside Diameter, 0.36 LB/MFT
Weight per unit	0.3600 (lbs/ft)
Product Category	Portable Cord Sets

Features

Cord Type	SPT-3, -20 to 60 Deg C
Inlet	Male Plug 90 Degree
Length in meters	1.2192
Voltage Rating	125 V

Dimensions and Weight

Length	4 FT
--------	------

Descriptions

Additional Information	Conductor 26/30 Bare Copper Stranded; Conductor Outer Diameter 0.059 Inch; Insulation Material PVC
Commodity Description	Portable Cord Sets
Description	4' 16/3 ANGLE CORD GRY

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892097240
Model	9724
UPC	029892097240

Taxonomies, Classifications, and Categories

Category Description	CORD SETS [DRYER & RANGE CORDS & BOOSTER CABLES)
----------------------	--

Packaging

Carton	1
Package	25
Weight Per foot	0.36

Uses, Certifications, and Standards

Approval	UL mA
Configuration	NEMA 5-15P



PRODUCT SPECIFICATION

COLEMAN PART NUMBER: 09724

DESCRIPTION: 16/2 w/gnd SPT-3 power supply cord with right angle attachment plug cap.

APPROVALS: UL Listed (UL 817)

CONSTRUCTION PARAMETERS:

Conductor:	16 AWG, 26/30 bunched bare copper
Conductor O.D. (nom):	0.063"
Insulated ground conductor O.D. (nom):	0.091"
Insulation material:	PVC, gray
Overall cable dimensions (nom):	0.181 x 0.413"
Attachment plug configuration:	NEMA 5-15P
Plug material:	PVC, gray
Open end configuration:	1.5" separation, 0.38" strip

ELECTRICAL PROPERTIES:

Temperature rating:	-20 to +60 °C
Maximum operating voltage:	125 VAC
Maximum operating current:	13 A
Maximum operating wattage:	1625 W

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Systems. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Systems.

CUSTOMER APPROVAL: Approved by: _____ Date: _____
Title: _____