



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

801 Sterlington Rd.
71203-0000, LA Monroe
Phone: 318-387-1621
Fax: 318-387-1763



2424812 Encl 24X24X8 N12 1DR WM CH *Cooper B-Line/Cable Tray*

Catalog Number	2424812
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 24" Height, 8" Length, 24" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	45.3 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	8.0000 IN X 24.0000 IN X 24.0000 IN
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	24.00 In Width X 8.00 In Depth X 24.00 In Height
------	--

Descriptions

Description	ENCL 24X24X8 N12 1DR WM CH
extra long description	B-LINE 24248-12 TYPE 12 SGL-DOOR EN
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 24" height, 8" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 24X24X8
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051801507
Manufacturers Part Number	24248-12
UPC	782051801507

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

801 Sterlington Rd.
71203-0000, LA Monroe
Phone: 318-387-1621
Fax: 318-387-1763

Packaging

Carton	1
Weight Per each	45.335

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherGeneration - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Building Automation and MonitoringCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsDatacenters - IT Space: CI and Hyper ConvergedCommercial / Institutional Buildings / Structures - Critical PowerOther IT and Datacom - IT and Datacomm - OtherUtility - Substations, Uti
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	NEMA,UL 508A,CSA C22.2.