



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1003 As-3 Anti Short Bushings

*Bridgeport Fittings*

Catalog Number	1003
Manufacturer	Bridgeport Fittings
Description	
Weight per unit	0.0025 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

### Features

Material	Plastic
media	Yes
Trade Size	3 in

### Material, Color, and Finish

Color	RED
Finish	PLAIN

### Dimensions and Weight

Size	3 W
------	-----

### Descriptions

Description	AS-3 ANTI SHORT BUSHINGS
Product Type	No-3 Anti-Short Bushing
Special Features	10/4, 8/2, 8/3, 1/1 AWG

### Manufacturer Information

Brand	Bridgeport
GTIN	00781747010032
Manufacturers Part Number	1003
UPC	781747010032

### Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	BUSHING

### Packaging


Carton	20
Weight Per each	0.0025

### Uses, Certifications, and Standards

Application	Polyethylene "Redheads" prevent damage to wire installation when placed between the wire and armored sheath. Rated 90 degree C.
standard	CSA, UL
Temperature Rating	90 WTT

## Anti-Short Bushings - Redheads

### Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 11/16

Dimension B in Inches: 1-1/16

### Application

Polyethylene "Redheads" prevent damage to wire installation when placed between the wire and armored sheath. Rated 90 degree C.

### Product Information

Material: Plastic

Finish: Plain

### Certifications & Codes:

CSA File Number: LR24719M5

NEMA Standard: FB-1

UL File Number: E11259

UL Standard: UL-514B

UNSPSC: 39121312

**Catalog ID:** 1003

**UPC Number:** 781747010032

**Description:** Bushing, Anti-Short, Redheads, Polyethylene, Trade Size 3

**Application:** Polyethylene "Redheads" prevent damage to wire installation when placed between the wire and armored sheath. Rated 90 degree C.

**Trade Size:** 3"

**Std Pkg Qty:** 2000

**Unit Qty:** 20