



KTLD-25-UV-SC1250-56-VDIM-W1 /USB CONSTANT CURRENT PROGRAMMABLE LED DRIVER

DESCRIPTION

LED Driver | 25W | 120-277V Input | 420-1250mA Programmable Output Current

TOTAL POWER: 25W	OUTPUT CURRENT: 420-1250mA
INPUT VOLTAGE: 120-277Vac ±10%	DIMMING: 0-10V
INPUT FREQUENCY: 50/60 Hz	WARRANTY: 5 Years

PRODUCT FEATURES

- Built in USB-C Port for easy programing
- Meets FCC Part 15 (Class B) Consumer Limits
- Short Circuit Overload and Open Load Protection
- Dimmable with 0-10V Dimmer (Down to 1% at Max. Output Current)
- Auxiliary Power: 12Vdc; 200mA Max.
- THD: < 20%

Input Frequency: 50/60 Hz
Programmable output current via USB-C cable and an Android

• 90°C/194°F Maximum Case Temperature

-20°C/-4°F to 50°C/122°F Operating Temperature

WHAT'S NEEDED? A Smart Current Programmable LED Driver, USB-C Cable,

and a computer or phone

- Programmable output current via OSB-C cable and an Android device (plus Keystone app) or PC (plus Keystone software)
 Class A Sound Rating
- PROGRAMMING FEATURES
 Drive Current (10mA Increments)
 Minimum Dimming Level (1%,3%, 5%,7%, or 10%)
 Dimming Curve (Linear, Log, Inverse Log, or Square-law)
 - Minimum Dimming Voltage (1V, 1.5V, or 2V)
 - Maximum Dimming Voltage (7V, 8V, or 9V)
 - Dim-to-off Voltage (.8V, 1V, 1.2V, or N/A)
 - Thermal Foldback Temperature (75°C/167°F, 80°C/176°F, 85°C/185°F, or 90°C/194°F)

REQUIRED ACCESSORIES

Order Code	Description
KTLD-SC-USBC	USB-C to USB-C Cable (included with driver)

ELECTRICAL SPECIFICATIONS

Input Voltage Range	120-277Vac ±10%				
Frequency	50/60 Hz				
Power Factor	>0.9 under 120~277Vac Input with 80~100% Load Condition (For All Output Currents)				
Inrush Current	24A _{peak} @ 277Vac ; i ² t = 0.01728 A ² s				
Max. Input Current 0.29A @120V, 0.15A @240V and 0.13A @277V					
THD	< 20% under 120~277Vac input with 80~100% load condition (For All Output Currents)				
Load Regulation	± 2%				
Line Regulation	± 1%				
Output Tolerance	± 5% at Full Load Condition				
Turn-On Delay Time	< 2 Seconds at Full Load Condition				
Overshoot	< 10% at Full Load Condition				
No Load Power Consumption	< 1W				
Ripple and Noise (pk-pk)	< 3%				
Withstand Voltage	Input to output, 2,800Vdc, 2mA				
Leakage Current	Maximum 0.5mA at 277Vac, 60Hz input				
	 Over Voltage Protection: Hiccup mode. Protection will trigger when load voltage exceed specified output voltage and will auto recover after the fault mode is removed. Over Current Protection: Hiccup mode. Protection will trigger when load current exceed specified output current and will auto recover 				
Protection	after the fault mode is removed.				
	 Short Circuit Protection: Hiccup mode. Protection will trigger when short circuit and will auto recover after the fault mode is removed. Over Temperature Protection: Protection will trigger when driver overheat and auto-recovery when cooled down. 				



KEYSTONE

56.0V

Programmed Output Current Setting

580

[1400mA]

mΑ

50.0W

DIM-to-OFF






KTLD-25-UV-SC1250-56-VDIM-W1 /USB CONSTANT CURRENT PROGRAMMABLE LED DRIVER

PRODUCT SPECIFICATIONS

Max.		Output	OCV	Typical Efficiency at 120V	Typical Efficiency at 240V	Typical Efficiency at 277V	Remote Mount- ing Distance (#18 AWG)	Class 2	
Output Power		Voltage						US	Canada
25W	420-1250mA	10-56V	60V	86%	87%	87%	29 ft.	1	


PHYSICAL SPECIFICATIONS



U	113	
	LENGTH	5.00"
	WIDTH	2.38"
	HEIGHT	1.00″
н	MOUNTING	4.62"
Ľ	CASE STYLE	W1
	CASE MATE- RIAL	Metal

WIRING SPECIFICATIONS

INPUT	Terminal Block	
OUTPUT	Terminal Block	
DIMMING	Terminal Block	



ENVIRONMENTAL SPECIFICATIONS

Operating Temperature	-20 to 50°C
Storage Temperature	-40 to 85°C
Humidity	5% to 95%
MTBF	TBD
Life Rating	85,000 hours at 120Vac input, 100% load and 60°C case temperature
Maximum Case Temperature	90°C






KTLD-25-UV-SC1250-56-VDIM-W1 /USB CONSTANT CURRENT PROGRAMMABLE LED DRIVER

SAFETY AND EMC COMPLIANCE

UL/cUL	UL 8750 Pending, UL1310 Class 2
CE	EN61347-1, EN61347-2-13
FCC, 47CFR Part 15	ANSI C63.4:2009 Class B (Consumer Limit)
EN61000-3-2	Harmonic Current Emissions Class C

LED DRIVER OUTPUT WINDOW



Note: Driver is in Constant Power mode from 500mA to 1250mA.

ORDERING INFORMATION						
Order Code		Packaging Style	Pack Quantity	Item Status		
	KTLD-25-UV-SC1250-56-VDIM-W1 /USB	Carton Pack	50	Quick Ship		

CATALOG NUMBER BREAKDOWN

