

## SPECIFICATION SHEET

## 1109A-P

# Same ON/OFF Times Each Day



#### **APPLICATIONS:**

- Lighting, pumps, signs.
- Air conditioning, water heaters, fans.
- Automatic ON/OFF control when operation is required at the same time every day.



- Scheduling: Minimum ON is setting 20 minutes with a minimum OFF setting of 75 minutes.
  Dial accommodates up to 12 pairs of trippers. One pair included.
- Manual Override: Until the next regularly scheduled ON or OFF automatic operation then resumes.
- Standards: Listed UL/CSA 60730.
- Enclosed Motor: Protects gears for extended life.

### **SPECIFICATIONS:**

- Timing Accuracy: Line Frequency.
- Input Voltage: 120/208-277VAC, 50/60Hz
- Terminal Range: #8 #14AWG.
- Operating Temperature: -40 °F to 149 °F (-40 °C to 65 °C).
- Power Consumption: 3 Watts Max.
- Enclosure: Metal Indoor NEMA 1. Suffix -O Metal Indoor/Outdoor NEMA 3R. All with lockable hasp.



### **CONTACT RATINGS:**

- General Purpose: 120/208-277VAC 40A.
- Resistive: 120/208-277VAC 40A.
- Tungsten: 120VAC 40A.
- Ballast: 120/208-277VAC 20A.
- Electronic Ballast (LED): 120/208-277VAC 16A.
- Pilot Duty: 120VAC 1000VA, 240VAC 2000VA.
- Motor: 120VAC 2HP, 240VAC 5HP.
- Short Circuit Rating: 5KA (when protected by a Class T Fuse Rated 60A).

Cat. No.	Certification	UPC Code	Input Supply (VAC) 60Hz	Output Contacts	Enclosure Type
1109A-P	cULus	10106	120/208-277	SPST/DPST	Plastic Indoor/Outdoor NEMA 3R

