



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1225GRY Switch Manual Control 20A120/277V

Pass & Seymour/Legrand

Catalog Number	1225GRY
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Double-Throw Switch, 20A, 120/277V
Weight per unit	0.3030 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

amperage rating	20
Contact Configuration	NO
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	CFL, Universal, Halogen, LED, Incandescent, Xenon, Fluorescent
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	3
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Gray
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	SWITCH MANUAL CONTROL 20A120/277V
extra long description	P&S 1225GRY SWITCH MANUAL CONTRL 20
Features	Durable
Long Description	Single-Pole, Double-Throw Switch, 20A, 120/277V
Product Type	Switch Manual Contrl 20A120/277V
Special Features	Oversized silver alloy contacts, side wired, can be mounted in standard device box\



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007278996
Manufacturers Part Number	1225-GRY
UPC	785007278996

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Manual Controller, Tamper-Resistant

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.303

Uses, Certifications, and Standards

Application	Industrial
Enclosure	Box or NEMA 1 sheet steel
Mounting standard	WALL UL, CSA, CULUS, UL Listed