



SAFETY DATA SHEET

1. Identification

Product identifier	RTV Silicone Adhesive & Sealant - Clear (pressurized) - 6.5 oz
Other means of identification	
Product Code	No. 14055 (Item# 1004788)
Recommended use	Sealant and adhesive
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency (CHEMTREC)	800-424-9300 (US)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Gases under pressure	Compressed gas
Health hazards	Not classified.	
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	
Label elements		



Signal word	Warning
Hazard statement	Contains gas under pressure; may explode if heated.
Precautionary statement	
Prevention	Observe good industrial hygiene practices. Do not puncture or incinerate container. Do not expose to heat or store at temperatures above 49 °C/120 °F. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying.
Response	Wash hands after handling.
Storage	Protect from sunlight. Store in a well-ventilated place. Exposure to high temperature may cause can to burst.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	When heated to temperature above 300°F/150°C in the presence of air, product may form formaldehyde vapors. When exposed to water or humid air, product evolves acetic acid (HOAc).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
amorphous silica		7631-86-9	5 - 10

Chemical name	Common name and synonyms	CAS number	%
distillates (petroleum), hydrotreated middle		64742-46-7	5 - 10

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash with water and soap as a precaution. Get medical attention if irritation develops and persists.
Eye contact	Flush eyes with water as a precaution. If eye irritation persists: Get medical advice/attention.
Ingestion	If swallowed, do NOT induce vomiting. Get medical attention if symptoms occur. Rinse mouth thoroughly.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water. Alcohol resistant foam. Dry chemical powder. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved.
General fire hazards	Contents under pressure. Pressurized container may rupture when exposed to heat or flame.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Stop the flow of material, if this is without risk. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Observe good industrial hygiene practices. For product usage instructions, see the product label.
Conditions for safe storage, including any incompatibilities	Level 1 Aerosol. Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
distillates (petroleum), hydrotreated middle (CAS 64742-46-7)	PEL	5 mg/m3	Mist.

US. OSHA Table Z-3 (29 CFR 1910.1000)

Components	Type	Value
amorphous silica (CAS 7631-86-9)	TWA	0.8 mg/m3 20 mppcf

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
distillates (petroleum), hydrotreated middle (CAS 64742-46-7)	TWA	5 mg/m3	Inhalable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
amorphous silica (CAS 7631-86-9)	TWA	6 mg/m3	
distillates (petroleum), hydrotreated middle (CAS 64742-46-7)	STEL	10 mg/m3	Mist.
	TWA	5 mg/m3	Mist.

Biological limit values

No biological exposure limits noted for the ingredient(s).

Exposure guidelines

Occupational Exposure Limits are not relevant to the current physical form of the product.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear protective gloves such as: Nitrile. Butyl rubber.

Other

Wear appropriate chemical resistant clothing.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Observe any medical surveillance requirements. When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

9. Physical and chemical properties

Appearance

Physical state Solid, Liquid.

Form Paste.

Color Translucent.

Odor Acetic acid.

Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	680 °F (360 °C) estimated
Flash point	> 212 °F (> 100 °C)
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapor pressure	4.2 hPa estimated
Vapor density	Not available.
Relative density	1.01
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	500 °F (260 °C) estimated
Decomposition temperature	Not available.
Percent volatile	< 3 %

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Heat, flames and sparks. Contact with incompatible materials. When heated to temperature above 300°F/150°C in the presence of air, product may form formaldehyde vapors. When exposed to water or humid air, product evolves acetic acid (HOAc).
Incompatible materials	Strong oxidizing agents. Water, moisture.
Hazardous decomposition products	Carbon oxides. Silicone oxides. Formaldehyde.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	Prolonged skin contact may cause temporary irritation.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	Health injuries are not known or expected under normal use.

Symptoms related to the physical, chemical and toxicological characteristics Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

Acute toxicity Not known.

Components	Species	Test Results
amorphous silica (CAS 7631-86-9)		
<u>Acute</u>		
Oral		
LD50	Rat	> 22500 mg/kg

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory or skin sensitization	
Respiratory sensitization	Not a respiratory sensitizer.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
IARC Monographs. Overall Evaluation of Carcinogenicity	
amorphous silica (CAS 7631-86-9)	3 Not classifiable as to carcinogenicity to humans.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)	
Not regulated.	
US. National Toxicology Program (NTP) Report on Carcinogens	
Not listed.	
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not an aspiration hazard.

12. Ecological information

Ecotoxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
Bioaccumulative potential	
Mobility in soil	No data available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Hazardous waste code	Not regulated.
Disposal instructions	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Consult authorities before disposal. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.



14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Label(s)	2.2
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

IATA

UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity

Transport hazard class(es)**Class** 2.2**Subsidiary risk** -**Packing group** Not applicable.**ERG Code** 2L**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.**Other information****Passenger and cargo aircraft** Allowed with restrictions.**Cargo aircraft only** Allowed with restrictions.**IMDG****UN number** UN1950**UN proper shipping name** AEROSOLS, Limited Quantity**Transport hazard class(es)****Class** 2.2**Subsidiary risk** -**Packing group** Not applicable.**Environmental hazards****Marine pollutant** No.**EmS** Not available.**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.**DOT; IMDG****IATA**

15. Regulatory information**US federal regulations**

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories Gas under pressure

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Not regulated.

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Massachusetts RTK - Substance List

amorphous silica (CAS 7631-86-9)

US. Pennsylvania Worker and Community Right-to-Know Law

amorphous silica (CAS 7631-86-9)

distillates (petroleum), hydrotreated middle (CAS 64742-46-7)

US. Rhode Island RTK

distillates (petroleum), hydrotreated middle (CAS 64742-46-7)

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrotreated middle (CAS 64742-46-7)

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) < 3 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products This product is regulated as a Sealant and Caulking Compound. This product is compliant for use in all 50 states.

VOC content (CA) < 3 %

VOC content (OTC) < 3 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No

Country(s) or region	Inventory name	On inventory (yes/no)*
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 09-17-2019

Prepared by Dustin Kern

Version # 01

Disclaimer The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

Revision information This document has undergone significant changes and should be reviewed in its entirety.