





FB31T8/830/1 Lamp Specifications

TCP Item Number: 31031830U1

Lamp code: FB31T8/830/1



Average Rated Life (hours) ----- 20,000

TCLP Compliant ----- Yes

Mercury Content (mg) ----- 8.0

Physical Characteristics

Lamp type ----- T8
Base type ----- BiPin (G13)
Lamp Material ----- Soda Lime
Phosphor ----- Tri-Phosphor
Lamp Diameter (inches)
Nominal (D) ----- 1.00
Maximum (D) ----- 1.10
Minimum (D) ----- 0.94
Base Center to Base Center (inches) (C) --- 1.625
Base Face to Top of Lamp (inches) (B) ----- 22.325
Nominal Overall Length (inches) (A) ----- 22.325

Photometric Characteristics


Initial Lumens ----- 2750
Mean Lumens (40% of rated life) ----- 2600
Correlated Color Temperature (Kelvin) ----- 3000
Color Rendering Index (CRI) ----- 85
Normal Efficacy (Lumens/Watts) ----- 89

Electrical Characteristics


Lamp Watts ----- 31
Nominal Lamp Volts ----- 135
Nominal Lamp Operating Frequency (Hz) -- 50-60 Hz
Min. Starting Lamp Voltage at 10°C ----- 300
Filament Volts (V) ----- 3.4
Max. Current Crest Factor ----- 1.7

24 MONTH
STANDARD WARRANTY


Spectral Power Distribution



Lamp Lumen Maintenance



Typical Lamp Mortality



For the most up-to-date specs, please visit www.tcpi.com

TCP, Inc.

325 Campus Dr. | Aurora, Ohio 44202 | P: 1-800-324-1496 | F: 330-995-6188 | tcpi.com

©TCP, Inc. AUG 2013/51033

TCP is proud to have been awarded
ENERGY STAR® Partner of the Year 2013.







FB31T8/830/1 Lamp Specifications

TCP Item Number: 31031830U1

Lamp code: FB31T8/830/1



Average Rated Life (hours) ----- 20,000

TCLP Compliant ----- Yes

Mercury Content (mg) ----- 8.0

Physical Characteristics

Lamp type ----- T8
Base type ----- BiPin (G13)
Lamp Material ----- Soda Lime
Phosphor ----- Tri-Phosphor
Lamp Diameter (inches)
Nominal (D) ----- 1.00
Maximum (D) ----- 1.10
Minimum (D) ----- 0.94
Base Center to Base Center (inches) (C) --- 1.625
Base Face to Top of Lamp (inches) (B) ----- 22.325
Nominal Overall Length (inches) (A) ----- 22.325

Photometric Characteristics


Initial Lumens ----- 2750
Mean Lumens (40% of rated life) ----- 2600
Correlated Color Temperature (Kelvin) ----- 3000
Color Rendering Index (CRI) ----- 85
Normal Efficacy (Lumens/Watts) ----- 89

Electrical Characteristics


Lamp Watts ----- 31
Nominal Lamp Volts ----- 135
Nominal Lamp Operating Frequency (Hz) -- 50-60 Hz
Min. Starting Lamp Voltage at 10°C ----- 300
Filament Volts (V) ----- 3.4
Max. Current Crest Factor ----- 1.7

24 MONTH
STANDARD WARRANTY


Spectral Power Distribution



Lamp Lumen Maintenance



Typical Lamp Mortality



For the most up-to-date specs, please visit www.tcpi.com

TCP, Inc.

325 Campus Dr. | Aurora, Ohio 44202 | P: 1-800-324-1496 | F: 330-995-6188 | tcpi.com

©TCP, Inc. AUG 2013/51033

TCP is proud to have been awarded
ENERGY STAR® Partner of the Year 2013.

