

# Eaton 1433

Catalog Number: 1433

Eaton Arrow Hart severe duty straight blade plug,#14-8 AWG,20A,Industrial,125V,Back wire,Yellow,black,Nickel-plated brass,Corrosion Resistant,Nylon,5-20P,Two pole,three wire,grounding,Screw,0.38-1" in diameter,Thermoplastic,Core pack

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart severe duty straight blade plug	1433
	<b>UPC</b>
	040893630830
<b>Product Length/Depth</b>	<b>Product Height</b>
1.69 in	1.75 in
<b>Product Width</b>	<b>Product Weight</b>
1.69 in	0.135 lb
<b>Warranty</b>	<b>Certifications</b>
Refer to warranty document.	cULus Listed

## Product specifications

### Device type

Plug

### Color

Black

Yellow

### Face/body material

Nylon

### Wiring method

Back wire

### Material

Thermoplastic

### Allowable wire size

#14-8 AWG

### Amperage Rating

20A

### Number Of Poles

Two-pole

### Contact material

Nickel plated brass

### Type

Complex environment

### Device grade

Severe duty

### NEMA configuration

5-20P

### Style type

Straight body

### Environmental conditions

Corrosive

### Design type

Straight blade

### Environmental resistance

Corrosion resistant

### Connection type

Screw

## Resources

### Brochures

[Complex environment devices brochure](#)

[Wiring Devices Buyer's Guide](#)

### Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1433](#)

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Cord range

0.38-1" in diameter

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

Core pack



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)