






FB32T8/841/6 Lamp Specifications

TCP Item Number:
31032841U6

Lamp code:
FB32T8/841/6



Cathode Guarded

Average Rated Life (hours) ----- 20,000
TCLP Compliant ----- Yes
Low Mercury ----- Yes

Physical Characteristics

Lamp type ----- T8
Base type ----- BiPin (G13)
Lamp Material ----- Soda Lime
Phosphor ----- Tri-Phosphor
Lamp Diameter (inches)
Nominal (D) ----- 1.00
Maximum (D) ----- 1.10
Minimum (D) ----- 0.94
Base Center to Base Center (inches) (C) --- 6.00
Base Face to Top of Lamp (inches) (B) ----- 22.60
Nominal Overall Length (inches) (A) ----- 23.00

Photometric Characteristics


Initial Lumens ----- 3000
Mean Lumens (40% of rated life) ----- 2850
Correlated Color Temperature (Kelvin) ----- 4100
Color Rendering Index (CRI) ----- 85
Normal Efficacy (Lumens/Watts) ----- 93.75

Electrical Characteristics


Lamp Watts ----- 32
Nominal Lamp Volts ----- 137
Nominal Lamp Operating Frequency (Hz) -- 50-60 Hz
Min. Starting Lamp Voltage at 10°C ----- 300
Filament Volts (V) ----- 3.4
Max. Current Crest Factor ----- 1.7

24 MONTH
STANDARD WARRANTY


Spectral Power Distribution



Lamp Lumen Maintenance



Typical Lamp Mortality



For the most up-to-date specs, please visit www.tcpi.com

TCP, Inc.
325 Campus Dr. | Aurora, Ohio 44202 | P: 1-800-324-1496 | F: 330-995-6188 | tcpi.com
©TCP, Inc. SEPT 2013/51038

TCP is proud to have been awarded
ENERGY STAR® Partner of the Year 2013.








FB32T8/841/6 Lamp Specifications

TCP Item Number:
31032841U6

Lamp code:
FB32T8/841/6



Cathode Guarded

Average Rated Life (hours) ----- 20,000
TCLP Compliant ----- Yes
Low Mercury ----- Yes

Physical Characteristics

Lamp type ----- T8
Base type ----- BiPin (G13)
Lamp Material ----- Soda Lime
Phosphor ----- Tri-Phosphor
Lamp Diameter (inches)
Nominal (D) ----- 1.00
Maximum (D) ----- 1.10
Minimum (D) ----- 0.94
Base Center to Base Center (inches) (C) --- 6.00
Base Face to Top of Lamp (inches) (B) ---- 22.60
Nominal Overall Length (inches) (A) ----- 23.00

Photometric Characteristics


Initial Lumens ----- 3000
Mean Lumens (40% of rated life) ----- 2850
Correlated Color Temperature (Kelvin) ----- 4100
Color Rendering Index (CRI) ----- 85
Normal Efficacy (Lumens/Watts) ----- 93.75

Electrical Characteristics


Lamp Watts ----- 32
Nominal Lamp Volts ----- 137
Nominal Lamp Operating Frequency (Hz) -- 50-60 Hz
Min. Starting Lamp Voltage at 10°C ----- 300
Filament Volts (V) ----- 3.4
Max. Current Crest Factor ----- 1.7

24 MONTH
STANDARD WARRANTY


Spectral Power Distribution



Lamp Lumen Maintenance



Typical Lamp Mortality



For the most up-to-date specs, please visit www.tcpi.com

TCP, Inc.
325 Campus Dr. | Aurora, Ohio 44202 | P: 1-800-324-1496 | F: 330-995-6188 | tcpi.com
©TCP, Inc. SEPT 2013/51038

TCP is proud to have been awarded
ENERGY STAR® Partner of the Year 2013.

