



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2202 East Rusk Street  
75766-0000, TX Jacksonville  
Phone: 903-586-2904  
Fax: 903-586-5271



## 14H400 1/4" X 4" Slotted Hex Washer Head Concrete Screw

L.H. Dottie CO.

Catalog Number	14H400
Manufacturer	L.H. Dottie CO.
Description	Hex Head Concrete Anchor System, 1/4 In. Diameter, 4 In. Length, Hi-Low Thread Type, 3/16 X 5-1/2 In. Drill Size, Ceramic Coated Blue Finish, Drill Included, 5/16 In. Bit Size, Slotted Drive Type
Weight per unit	3.6 (lbs/each)
Product Category	Anchors & Fasteners

### Features

Bit Size	5/16
Drill Size	3/16 x 5-1/2
Drive Type	Slotted
Head Type	Hex
included	Drill
Material	Steel
Thread Size	1/4
Thread Type	Hi-Low

### Material, Color, and Finish

Finish	Ceramic Coated Blue
--------	---------------------

### Dimensions and Weight

Diameter	1/4
Length	4
Size	1/4 x 4

### Descriptions

Description	1/4" X 4" SLOTTED HEX WASHER HEAD CONCRETE SCREW
extra long description	DOTTIE 14H400 1/4 X 4" Hex Head Con
Long Description	Hex Head Concrete Anchor System, 1/4 in. diameter, 4 in. length, Hi-Low thread type, 3/16 x 5-1/2 in. drill size, Ceramic Coated Blue finish, Drill included, 5/16 in. bit size, Slotted drive type
Product Type	1/4 X 4" Hex Head Concrete Anchor System
Special Features	Features: Includes Drill, Hex Head Slotted

### Manufacturer Information

Brand	L.H. Dottie CO.
GTIN	00781002256489
Manufacturers Part Number	14H400
UPC	781002256489



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2202 East Rusk Street  
75766-0000, TX Jacksonville  
Phone: 903-586-2904  
Fax: 903-586-5271

## Taxonomies, Classifications, and Categories

Category Description ..... Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps  
Type ..... Hex Head Concrete Anchor System

## Packaging

Carton ..... 100  
Weight Per each ..... 3.6

## Uses, Certifications, and Standards

Application ..... Poured Concrete, Prestressed Concrete, Cinder Block, Brick,  
Mortar