


Atlanta, Georgia

Phone 800-521-7326


Fax 770-745-1333

Hex Lag Screws Zinc, Stainless, and Hot-Dip Galvanized



			E		F			G		H			S	
			Shoulder Diameter		Width			Width		Head Height			Shoulder Length	
					Across Flats			Across Corners						
Basic Diameter		Threads Per Inch	Min	Max	Basic	Min	Max	Min	Max	Basic	Min	Max	Min	
10	0.1900	11	0.178	0.199	9/32	0.271	0.281	0.309	0.323	1/8	0.110	0.140	0.094	
1/4	0.2500	10	0.237	0.260	7/16	0.425	0.438	0.484	0.505	11/64	0.150	0.188	0.094	
5/16	0.3125	9	0.298	0.324	1/2	0.484	0.500	0.552	0.577	7/32	0.195	0.235	0.125	
3/8	0.3750	7	0.360	0.388	9/16	0.544	0.562	0.620	0.650	1/4	0.226	0.268	0.125	
7/16	0.4375	7	0.421	0.452	5/8	0.603	0.625	0.687	0.722	19/64	0.272	0.316	0.156	
1/2	0.5000	6	0.482	0.515	3/4	0.725	0.750	0.826	0.866	11/32	0.302	0.364	0.156	
5/8	0.6250	5	0.605	0.642	15/16	0.906	.0938	1.033	1.083	27/64	0.378	0.444	0.312	
3/4	0.7500	4-1/2	0.729	0.768	1-1/8	1.088	1.125	1.240	1.299	1/2	0.455	0.524	0.375	
7/8	0.8750	4	0.852	0.895	1-5/16	1.269	1.312	1.447	1.516	37/64	0.531	0.604	0.375	
Tolerance on Length					Screw Size		Screw Length							
							Thru 6"		Over 6"					
					1/2 and smaller		±0.12		±0.25					
					Over 1/2		±0.25		±0.25					
Hardness Tensile Strength Material Minimum Thread Length Heat Treatment								1/4" through 1/2" Diameter Steel		1/4" through 1/2" Diameter Stainless Steel				
								Rockwell		B70 - B100		B95 - C32		
								psi		60,000 min		≈ 100,000 -125,000		
										AISI 1006-1022 or equivalent		18-8 Stainless		
								The minimum thread length is 1/2 of the length of the screw plus 1/2" or 5" whichever is shorter.						
								Stainless: The alloys develop their strength through work hardening during the manufacturing process. See hardness properties above. The only heat treatment normally available is annealing which is done at approximately 1900°F to a dead soft condition and is not reversible.						

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.




Atlanta, Georgia

Phone 800-521-7326

Fax 770-745-1333

Hex Lag Screws Zinc, Stainless, and Hot-Dip Galvanized



			E		F			G		H			S
			Shoulder Diameter		Width			Width		Head Height			Shoulder Length
					Across Flats			Across Corners					
Basic Diameter		Threads Per Inch	Min	Max	Basic	Min	Max	Min	Max	Basic	Min	Max	Min
10	0.1900	11	0.178	0.199	9/32	0.271	0.281	0.309	0.323	1/8	0.110	0.140	0.094
1/4	0.2500	10	0.237	0.260	7/16	0.425	0.438	0.484	0.505	11/64	0.150	0.188	0.094
5/16	0.3125	9	0.298	0.324	1/2	0.484	0.500	0.552	0.577	7/32	0.195	0.235	0.125
3/8	0.3750	7	0.360	0.388	9/16	0.544	0.562	0.620	0.650	1/4	0.226	0.268	0.125
7/16	0.4375	7	0.421	0.452	5/8	0.603	0.625	0.687	0.722	19/64	0.272	0.316	0.156
1/2	0.5000	6	0.482	0.515	3/4	0.725	0.750	0.826	0.866	11/32	0.302	0.364	0.156
5/8	0.6250	5	0.605	0.642	15/16	0.906	.0938	1.033	1.083	27/64	0.378	0.444	0.312
3/4	0.7500	4-1/2	0.729	0.768	1-1/8	1.088	1.125	1.240	1.299	1/2	0.455	0.524	0.375
7/8	0.8750	4	0.852	0.895	1-5/16	1.269	1.312	1.447	1.516	37/64	0.531	0.604	0.375
Tolerance on Length					Screw Size		Screw Length						
							Thru 6"		Over 6"				
					1/2 and smaller		±0.12		±0.25				
					Over 1/2		±0.25		±0.25				
Hardness Tensile Strength Material Minimum Thread Length Heat Treatment								1/4" through 1/2" Diameter Steel		1/4" through 1/2" Diameter Stainless Steel			
					Rockwell			B70 - B100		B95 - C32			
					psi			60,000 min		≈ 100,000 -125,000			
								AISI 1006-1022 or equivalent		18-8 Stainless			
					The minimum thread length is 1/2 of the length of the screw plus 1/2" or 5" whichever is shorter.								
					Stainless: The alloys develop their strength through work hardening during the manufacturing process. See hardness properties above. The only heat treatment normally available is annealing which is done at approximately 1900°F to a dead soft condition and is not reversible.								

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.