

Straight Blade Receptacles Tamper-Resistant GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




Pass & Seymour

Straight Blade Receptacles

Features	
<ul style="list-style-type: none"> ■ Protects children: patented shutter system helps prevent improper insertion of foreign objects. ■ Meets National Electrical Code® Tamper-Resistant requirements. ■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. ■ Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. ■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. ■ FSUL Listed (Federal Specification WC596). ■ Trip indicator light (red LED). ■ Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. 	<ul style="list-style-type: none"> ■ Two back wire holes per terminal. ■ Ground screw has a back wire clamp for easy installation. ■ 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. ■ Mounting screws are shipped captive in the device and wall plate for easier installation. ■ High-impact-resistant thermoplastic construction. ■ Extra-long strap. ■ Button colors match the device face. ■ Dual-direction test and reset buttons. ■ Class A rated GFCI. ■ Supplied with matching TP26 nylon wall plate. ■ Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> ■ Supply Voltage: 125VAC, 60 Hz ■ Supply Voltage Range: 102-132 VAC ■ Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> ■ Trip Time: 0.025 sec., nominal per UL Standard ■ 20 Amp feed-thru capacity





1595TRW



2095TRSW

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL _{US} UL943 C22.2 No. 144	cUL _{US} UL498 C22.2 No. 42	FSUL WC596
TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI							
1595TRI	15	125	Ivory	5-15R	•	•	•
1595TRW	15	125	White	5-15R	•	•	•
1595TR	15	125	Brown	5-15R	•	•	•
1595TRBK	15	125	Black	5-15R	•	•	•
1595TRLA	15	125	Light Almond	5-15R	•	•	•
1595TRBNCC4	15	125	Brushed Nickel	5-15R	•	•	•
1595TRTI	15	125	Titanium	5-15R	•	•	•
TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI with Auto-Ground							
1595TRSI	15	125	Ivory	5-15R	•	•	•
1595TRSW	15	125	White	5-15R	•	•	•
1595TRSLA	15	125	Light Almond	5-15R	•	•	•
Specification Grade Tamper-Resistant 20 Amp Duplex GFCI							
2095TRI	20	125	Ivory	5-20R	•	•	•
2095TRW	20	125	White	5-20R	•	•	•
2095TR	20	125	Brown	5-20R	•	•	•
2095TRGRY	20	125	Gray	5-20R	•	•	•
2095TRBK	20	125	Black	5-20R	•	•	•
2095TRRED	20	125	Red	5-20R	•	•	•
2095TRLA	20	125	Light Almond	5-20R	•	•	•
Specification Grade Tamper-Resistant 20 Amp Duplex GFCI with Auto-Ground							
2095TRSI	20	125	Ivory	5-20R	•	•	•
2095TRSW	20	125	White	5-20R	•	•	•
2095TRSLA	20	125	Light Almond	5-20R	•	•	•



National Electrical Code® Section 406.11 Tamper-Resistant Receptacles in Dwelling Units.

In all areas specified in 210.52 all 125-volt, 15- and 20-amp receptacles shall be listed tamper-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Tamper-Resistant GFCI Receptacles

Devices & Wall Plates Color Selection Chart




Pass & Seymour

Devices & Plastic Wall Plate Colors




Ivory Light Almond White Green



Black Blue Brown Gray Orange Red


See specific device and wall plate catalog charts for particular color availabilities.

Metal Wall Plates



Metal Finish Aluminum Brass (Brushed) Polished Brass Stainless Steel Brushed Bronze Chrome

Custom Metal Wall Plates Paint Finish Colors



Paint Color Orange Green Gray Yellow Glossy Black Brown White



Paint Color Primer Red Pink Flat Black Ivory Light Almond Blue

To order custom metal wall plates, see Pages Q-43 – Q-45.

For additional colors consult factory.

Technical Specifications Tamper-Resistant GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




Pass & Seymour

Typical Specifications	
Manufacturer's Identification: Legrand/Pass & Seymour 1595TR	
Description: Straight Blade Duplex Tamper-Resistant GFCI Receptacle	
Type: 2 Pole, 3 Wire Grounding	
Rating: 20A, 125VAC Feed Thru; 15 or 20A, 125VAC Face	
3rd Party Compliance: cULus Listed, File Number E42190; Standard UL498 Tamper-Resistant, Attachment Plugs and Receptacles UL943 GFCIs. Federal Specification WC596. Standard CSA-C22.2 No. 42, General Use Receptacles, CSA-C22.2 No. 144 GFCIs. Conforms to NEMA WD-1 and WD-6.	

Catalog Number	Color	Rating	NEMA Configuration No.
<input type="checkbox"/> 1595TRI	Ivory	15A 125VAC	5-15R
<input type="checkbox"/> 1595TRW	White	15A 125VAC	5-15R
<input type="checkbox"/> 1595TR	Brown	15A 125VAC	5-15R
<input type="checkbox"/> 1595TRBK	Black	15A 125VAC	5-15R
<input type="checkbox"/> 1595TRLA	Light Almond	15A 125VAC	5-15R
<input type="checkbox"/> 1595TRBNCC4	Brushed Nickel	15A 125VAC	5-15R
<input type="checkbox"/> 1595TRTI	Titanium	15A 125VAC	5-15R
<input type="checkbox"/> 1595TRSI*	Ivory	15A 125VAC	5-15R
<input type="checkbox"/> 1595TRSW*	White	15A 125VAC	5-15R
<input type="checkbox"/> 1595TRSLA*	Light Almond	15A 125VAC	5-15R
<input type="checkbox"/> 2095TRI	Ivory	20A 125VAC	5-20R
<input type="checkbox"/> 2095TRW	White	20A 125VAC	5-20R
<input type="checkbox"/> 2095TR	Brown	20A 125VAC	5-20R
<input type="checkbox"/> 2095TRGRY	Gray	20A 125VAC	5-20R
<input type="checkbox"/> 2095TRBK	Black	20A 125VAC	5-20R
<input type="checkbox"/> 2095TRRED	Red	20A 125VAC	5-20R
<input type="checkbox"/> 2095TRLA	Light Almond	20A 125VAC	5-20R
<input type="checkbox"/> 2095TRSI*	Ivory	20A 125VAC	5-20R
<input type="checkbox"/> 2095TRSW*	White	20A 125VAC	5-20R
<input type="checkbox"/> 2095TRSLA*	Light Almond	20A 125VAC	5-20R





Dimensions for
15 & 20 Amp



Dimensions for
15 & 20 Amp
With Auto-Ground

Performance			
Electrical			
Dielectric	Withstands 1500V minimum		
Trip Level	4 to 6 mA		
Trip Time	.025 Second Nominal		
Frequency	60 Hz		
Voltage	125VAC		
Voltage Range	102-132VAC		
Mechanical			
Indicator Light (LED)	Red, ON when GFCI is tripped		
Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)		
Terminal Accommodation	#14 – #10 AWG solid or stranded copper conductor only		
Product Identification	Ratings are a permanent part of device		
Environmental			
Operating Temperature	-35°C to +66°C		
Maximum Humidity	95%		
Flammability	UL94 V2		
Materials			
Face	Nylon	Hex Head Grounding Screw	Steel (Green)
Body	Nylon	Flat Head Mounting Screws	Zinc-Plated Steel
Contacts	.03" Brass (.8)	Test/Reset Buttons	Nylon
Mounting Straps	.05" Zinc-Plated Steel (1.3)	Tamper-Resistant Shutter	Thermoplastic
Terminal Screws	Steel #8 - 32	Auto-Ground Clip*	Brass Alloy C260



*Tamper-Resistant GFCIs with Auto-Ground feature.

Project
Location/Type