ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10650 West Airport Suite 100
77477-0000, TX Stafford
Phone: 281-879-4911
Fax: 281-879-8596



3232TREXWR Cca Resi Receptacle 15A TR WR BN

Pass & Seymour/Legrand

Catalog Number	3232TREXWR
Manufacturer	Pass & Seymour/Legrand
Description	Save Time and Reduce The Risk Of Improper Wiring With The 15A Tamper-Resistant External Pressure Plated Duplex Receptacle. The External Pressure Plate Expedites Installation, Requiring No Need to Loop The Wire. It Also Provides Additional Space to Easily Fit Larger Wire Gauge Sizes, Up to #10 Wires. Also Including Tamper and Weather* Resistance, This Model Was Designed For Use In Outdoor Spaces.
Weight per unit	N/A
Product Category	Wiring Devices

Features

indoor/outdoor	Outdoor
Number of Wires	3
Outlet Type	Tamper-Resistant, Weather-Resistant
Voltage	125.0 V
Wall Plate Included	NO
Wire Size	14 - 10

Descriptions

Description	CCA RESI RECEPTACLE 15A TR WR BN
extra long description	PAS 3232TREXWR CCA RESI RECEPTACLE
Features	Weatherproof
Long Description	Save time and reduce the risk of improper wiring with the 15A Tamper-Resistant External Pressure Plated Duplex Receptacle. The external pressure plate expedites installation, requiring no need to loop the wire. It also provides additional space to easily fit larger wire gauge sizes, up to #10 wires. Also including tamper and weather* resistance, this model was designed for use in outdoor spaces.
Product Type	Cca Resi Receptacle 15A TR WR BN

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007503685
Manufacturers Part Number	3232TREXWR
UPC	785007503685

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10650 West Airport Suite 100
77477-0000, TX Stafford
Phone: 281-879-4911
Fax: 281-879-8596

Trade Size

Amperage	15.0

Packaging

Carton	10
Package	200
Weight Per each	0

Uses, Certifications, and Standards

standard	CULUS, UL 498