

Eaton 3BR3042B150

Catalog Number: 3BR3042B150

Eaton BR main breaker loadcenter, No feed-thru lugs, Main circuit breaker, 150 A, L1, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CC, 42 Circuits, 30 Spaces, Four-wire, Three-phase, #1-3/0 AWG Cu/Al, Combination, NEMA 1, 208 Y/120, 240 V

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	3BR3042B150
UPC	Product Length/Depth
786676440455	3.88 in
Product Height	Product Width
27 in	14.31 in
Product Weight	Warranty
23 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.



Product specifications

Number of spaces

30

Special features

No feed-thru lugs

Interrupt rating

10 kAIC

Phase

Three-phase

Wire size

#1-3/0 AWG Cu/Al

Bus material

Aluminum

Main circuit breaker

CC

Enclosure

NEMA 1

Amperage Rating

150 A

Mounting

Combination

Enclosure material

Metallic

Type

Main circuit breaker

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 1

Number of wires

4

Number of circuits

42

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, CC MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 3 PHASE

Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR3042B150

Voltage rating

208Y/120, 240V

Box size

L1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)