

Eaton 3BR3042B200

Catalog Number: 3BR3042B200

Eaton BR main breaker loadcenter, No feed-thru lugs, Main circuit breaker CC, 200 A, L1, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, 42-Ckt, 30 Spaces, 4-wire, Three-phase, #1 AWG-250 kcmil Cu/Al, Combination, 208 Y/120, 240 V



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	3BR3042B200
UPC	Product Length/Depth
786676440707	3.88 in
Product Height	Product Width
4.5 in	14.31 in
Product Weight	Warranty
23 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.

defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs

Type

Main circuit breaker

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CC

Number of circuits

42

Number of spaces

30

Phase

Three-phase

Wire size

#1 AWG-250 kcmil Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

208Y/120, 240V

Box size

L1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, CC MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 3 PHASE

Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR3042B200

Number of wires

4

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)